


1 KEYING RIBS; CUTTING WITH TERMINATION MACHINE POSSIBLE



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN	17-Nov-21							
DIMENSIONS: mm 						CHE	Winter Wang		TE Connectivity					
							Daniel Zhang		15-Mar-17					
							Riccardo Robone		13-Mar-17					
							Riccardo Robone							
TOLERANCES UNLESS OTHERWISE SPECIFIED:						NAME	DUOPLUG MARK II SIDE LOCKING							
0 P/LC ±							PRODUCT SPEC	-						
1 P/LC ±0.2							APPLICATION SPEC	108-18785-I						
2 P/LC ±								114-18467-I						
3 P/LC ±0.2							SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
ANGLES ±							A1	G=2306286	-					
FINISH						WEIGHT			-					
MATERIAL	-	-	-	-	-	CUSTOMER DRAWING								
-	-	-	-	-	-	SCALE		8:1	SHEET	1	OF	2	REP	B18

REVISIONS					
P	LYR	DESCRIPTION	DATE	OWN	APVD
-	-	SEE SHEET 1	-	-	-

GWEPT 750°C NO FLAME & UL94-VO, SILVER PLATED VERSION																		
-		X	X	X	X	X	X	X	X	9	20.0	24.9	23.5	20.0	3.75	2/3	1-2369990-9	
Red							X	X	X	4	7.5	12.4	11.0	7.5	6.25	3/4	1-2369990-4	
Color Code	10	9	8	7	6	5	4	3	2	1	POS.	A	B	C	D	E	 KEYING	PN Bestell-Nr.
CAVITIES LOADED																		

GWEPT 750°C NO FLAME & UL94-VO, TIN PLATED VERSION																							
-	X	0	X	X	0	X	0	X	0	X	10	22.5	27.4	26	22.5	6.25	3/4	1-2306287-0					
-	X	X	X	X	X	X	X	X	X	X						3.75	2/3	1-2306286-0					
-			X	X	X	X	X	X	X	X	9	20	24.9	23.5	20	3.75	2/3	1-2306286-9					
Black			X	X	X	X	X	X	X	X							2/3	2306286-9					
-			X	0	X	0	X	0	X	0							2/3	3-2306287-9					
-			X	0	X	X	0	X	0	X							2/3	2-2306287-9					
-			X	X	0	X	0	X	0	X						-	-	1-2306287-9					
Green			X	0	X	X	0	X	0	X						3.75	2/3	2306287-9					
				X	0	X	0	X	X	X	8	17.5	22.4	21	17.5	3.75	2/3	2306287-8					
-				X	X	X	X	X	X	X						11.25	5/6	1-2306286-8					
-				X	X	X	X	X	X	X						3.75	2/3	2306286-8					
Black					X	0	X	0	X	0	7	15	19.9	18.5	15	8.75	4/5	2-2306287-7					
-					X	0	X	0	X	0							2/3	1-2306287-7					
Blue					X	0	X	0	X	0						3.75	2/3	2306287-7					
					X	X	X	X	X	X						11.25	5/6	2-2306286-7					
-					X	X	X	X	X	X						3.75	2/3	1-2306286-7					
Black					X	X	X	X	X	X						2/3	2306286-7						
-						X	X	X	X	X	6	12.5	17.4	16	12.5	8.75	4/5	2-2306286-6					
-						X	X	X	X	X						3.75	2/3	1-2306286-6					
-						X	X	X	X	X						1.25	1/2	2306286-6					
-						X	0	X	X	0						3.75	2/3	4-2306287-6					
-						X	X	0	X	0						8.75	4/5	3-2306287-6					
-						X	0	X	X	0							4/5	2-2306287-6					
-						X	0	X	X	0						3.75	2/3	1-2306287-6					
Black						X	0	X	X	0						3.75	2/3	2306287-6					
-							X	0	X	0	5	10	14.9	13.5	10	3.75	2/3	2-2306287-5					
-							X	X	X	0						6.25	3/4	1-2306287-5					
Blue							X	X	X	0						6.25	3/4	2306287-5					
-							X	X	X	X						1.25	1/2	5-2306286-5					
-							X	X	X	X						6.25	3/4	4-2306286-5					
-							X	X	X	X						3.75	2/3	3-2306286-5					
Green							X	X	X	X						1.25	1/2	2-2306286-5					
Red							X	X	X	X						6.25	3/4	1-2306286-5					
Black							X	X	X	X						3.75	2/3	2306286-5					
-								X	X	X	4	7.5	12.4	11	7.5	6.25	3/4	3-2306286-4					
-								X	X	X						1.25	1/2	2-2306286-4					
Red								X	X	X						6.25	3/4	1-2306286-4					
Black								X	X	X						1.25	1/2	2306286-4					
-									X	0	3	5	9.9	8.5	5	1.25	1/2	3-2306287-3					
-									X	0						3.75	2/3	2-2306287-3					
Green									X	0						1.25	1/2	1-2306287-3					
Blue									X	0						3.75	2/3	2306287-3					
-									X	X						3.75	2/3	3-2306286-3					
-									X	X						1.25	1/2	2-2306286-3					
Black									X	X						3.75	2/3	1-2306286-3					
Red									X	X						1.25	1/2	2306286-3					
Color Code	10	9	8	7	6	5	4	3	2	1						POS.	A	B	C	D	E		PN Bestell-Nr.
	CAVITIES LOADED																						KEYING

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN

17-Nov-21

CHK

Winter Wang

APVD

15-Mar-17

Daniel Zhong

15-Mar-17

Riccardo Robone

PRODUCT SPEC

108-18785-1

APPLICATION SPEC

114-18467-1

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

0 PLC ±0.2

1 PLC ±0.2

2 PLC ±0.2

3 PLC ±0.2

4 PLC ±0.2

ANGLES ±0.2

FINISH

-

NAME

DUOPLUG MARK II

SIDE LOCKING

-

SIZE

A 1

CAGE CODE

C=2306286

DRAWING NO

-

RESTRICTED TO

-

SCALE

8:1

SHEET

2

OF

2

REV

B 18