




1. CONTACTS INSTALLED IN ALL POSITIONS (-1 & -2 ONLY).

2 STEEL PER ASTM-A-109.

3 PLATED TIN, .000300 TO .000500 THICK PER ASTM-B-545 OVER COPPER, .000050 TO .000200 THICK PER AMS 2418.

4 SUPPLIED WITHOUT CONTACTS, BRACKET, LOCK TABS, LOCKWASHER & SCREW. SUPPLIED WITH KAPTON INSULATOR.

5 SUPPLIED WITHOUT CONTACTS, BRACKET, LOCK TABS, LOCKWASHER & SCREW. SUPPLIED WITH BLACK POLYCARBONATE INSULATOR.

OBSOLETE

PRELIMINARY- NOT RELEASED FOR PRODUCTION

PRELIMINARY- NOT RELEASED FOR PRODUCTION

5	--	--	2101233-4
4	--	--	2101233-3
WITH CONTACTS	.120 [3.05]	.165±.020 [4.18±0.51]	2101233-2
WITH CONTACTS	.080 [2.03]	.125±.020 [3.18±0.51]	2101233-1
REMARKS	P.C. BOARD THICKNESS; REF	DIM A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 2-27-09	TE Connectivity	
DIMENSIONS: INCHES		CHK R. LEASE 2-27-09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. LEASE 2-27-09	NAME	
0 PLC ± .005 [0.13]		PRODUCT SPEC	RCPT. ASSY. AMPLIMITE, 3C3, RIGHT ANGLE, SIZE 2, COAX	
1 PLC ± .005 [0.13]		APPLICATION SPEC	—	
2 PLC ± .005 [0.13]		WEIGHT	A1 00779 2101233	
3 PLC ± .005 [0.13]		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV G	
4 PLC ± .005 [0.13]				
5 PLC ± .005 [0.13]				
ANGLES ± .1°				
FINISH SEE CALLOUTS				