

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	COLOR	DIMENSIONS in. [mm]				MAX WIRE INSUL DIA	WIRE STRIP LENGTH in [mm] + 1/32 [0.8] -0	TOOLS
			L ± .04 [1,1]	W ± .01 [0,3]	C ± .02 [0,4]	M ± .02 [0,6]			
EBNF18-4FIB	#22-16 [0.5-1.5]	RED	.99 [25.2]	.15 [3.9]	.28 [7.0]	.43 [11.0]	.145 [3.7]	9/32" [6.8]	KST2000C
EBNF14-4FIB*	#16-14 [1.5-2.5]	BLUE	.99 [25.2]	.15 [3.9]	.28 [7.0]	.43 [11.0]	.165 [4.2]		


*NOT UL RECOGNIZED

NOTES:

- UL RECOGNIZED FOR:
 - STRANDED COPPER WIRE ONLY - INTERNAL WIRING
 - NOT FOR INTERRUPTING CURRENT
 - 185°F (85°C) MAX TEMP RATING
 - 600V MAX VOLTAGE RATING
- MATERIAL:
 - STAMPING - .016" [0.4] THICK BRASS, TIN PLATED
 - HOUSING - NYLON
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.



E466810



TITLE STRONGHOLD FEMALE BULLET CONNECTORS (156 SERIES) FULLY NYLON INSULATED, #22-14 AWG CUSTOMER DRAWING				
ITEM REVISION NAME		00123SSP/00		
DATASET FILE NAME		00123SSP/00		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5°		MATERIAL: SEE NOTES		
THIRD ANGLE PROJECTION		DRAWING NUMBER: 00123SSP-DC		
DRAWN BY	DATE	CHK	SCALE	SIZE
JHNU	2/18		NONE	A
SHT 1 OF 1				

00	2/18	JHNU	TMR	RGB	DRAWING RELEASED	00123SS
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN