






DIALIGHT PART NUMBER	LED COLOR		
	POSITION 1	POSITION 2	POSITION 3
564-0100-002F	** BLANK **	** BLANK **	GREEN DIFFUSED
564-0100-010F	** BLANK **	RED DIFFUSED	** BLANK **
564-0100-011F	** BLANK **	RED DIFFUSED	RED DIFFUSED
564-0100-020F	** BLANK **	GREEN DIFFUSED	** BLANK **
564-0100-022F	** BLANK **	GREEN DIFFUSED	GREEN DIFFUSED
564-0100-030F	** BLANK **	YELLOW DIFFUSED	** BLANK **
564-0100-100F	RED DIFFUSED	** BLANK **	** BLANK **
564-0100-101F	RED DIFFUSED	** BLANK **	RED DIFFUSED
564-0100-102F	RED DIFFUSED	**BLANK**	GREEN DIFFUSED
564-0100-111F	RED DIFFUSED	RED DIFFUSED	RED DIFFUSED
564-0100-112F	RED DIFFUSED	RED DIFFUSED	GREEN DIFFUSED
564-0100-113F	RED DIFFUSED	RED DIFFUSED	YELLOW DIFFUSED
564-0100-120F	RED DIFFUSED	GREEN DIFFUSED	** BLANK **
564-0100-121F	RED DIFFUSED	GREEN DIFFUSED	RED DIFFUSED
564-0100-122F	RED DIFFUSED	GREEN DIFFUSED	GREEN DIFFUSED
564-0100-123F	RED DIFFUSED	GREEN DIFFUSED	YELLOW DIFFUSED
*564-0100-129F	RED DIFFUSED	GREEN DIFFUSED	BLUE (WHITE DIFF. EPOXY)
564-0100-132F	RED DIFFUSED	YELLOW DIFFUSED	GREEN DIFFUSED
564-0100-173F	RED DIFFUSED	ORANGE DIFFUSED	YELLOW DIFFUSED
564-0100-200F	GREEN DIFFUSED	** BLANK **	** BLANK **
564-0100-201F	GREEN DIFFUSED	** BLANK **	RED DIFFUSED
564-0100-202F	GREEN DIFFUSED	** BLANK **	GREEN DIFFUSED
564-0100-203F	GREEN DIFFUSED	** BLANK **	YELLOW DIFFUSED
564-0100-207F	GREEN DIFFUSED	** BLANK **	ORANGE DIFFUSED
564-0100-209F	GREEN DIFFUSED	** BLANK **	BLUE (WHITE DIFF. EPOXY)
564-0100-210F	GREEN DIFFUSED	RED DIFFUSED	** BLANK **
564-0100-211F	GREEN DIFFUSED	RED DIFFUSED	RED DIFFUSED
564-0100-212F	GREEN DIFFUSED	RED DIFFUSED	GREEN DIFFUSED
564-0100-213F	GREEN DIFFUSED	RED DIFFUSED	YELLOW DIFFUSED
564-0100-217F	GREEN DIFFUSED	RED DIFFUSED	ORANGE DIFFUSED
*564-0100-219F	GREEN DIFFUSED	RED DIFFUSED	BLUE (WHITE DIFF. EPOXY)
564-0100-220F	GREEN DIFFUSED	GREEN DIFFUSED	** BLANK **
564-0100-221F	GREEN DIFFUSED	GREEN DIFFUSED	RED DIFFUSED
564-0100-222F	GREEN DIFFUSED	GREEN DIFFUSED	GREEN DIFFUSED
564-0100-223F	GREEN DIFFUSED	GREEN DIFFUSED	YELLOW DIFFUSED
564-0100-227F	GREEN DIFFUSED	GREEN DIFFUSED	ORANGE DIFFUSED
*564-0100-229F	GREEN DIFFUSED	GREEN DIFFUSED	BLUE (WHITE DIFF. EPOXY)
564-0100-231F	GREEN DIFFUSED	YELLOW DIFFUSED	RED DIFFUSED
564-0100-232F	GREEN DIFFUSED	YELLOW DIFFUSED	GREEN DIFFUSED
564-0100-233F	GREEN DIFFUSED	YELLOW DIFFUSED	YELLOW DIFFUSED
564-0100-271F	GREEN DIFFUSED	ORANGE DIFFUSED	RED DIFFUSED
564-0100-277F	GREEN DIFFUSED	ORANGE DIFFUSED	ORANGE DIFFUSED
*564-0100-279F	GREEN DIFFUSED	ORANGE DIFFUSED	BLUE (WHITE DIFF. EPOXY)
*564-0100-291F	GREEN DIFFUSED	BLUE (WHITE DIFF. EPOXY)	RED DIFFUSED
*564-0100-299F	GREEN DIFFUSED	BLUE DIFFUSED	BLUE DIFFUSED
564-0100-300F	YELLOW DIFFUSED	** BLANK **	** BLANK **
564-0100-302F	YELLOW DIFFUSED	** BLANK **	GREEN DIFFUSED
564-0100-303F	YELLOW DIFFUSED	** BLANK **	YELLOW DIFFUSED
564-0100-311F	YELLOW DIFFUSED	RED DIFFUSED	RED DIFFUSED
564-0100-312F	YELLOW DIFFUSED	RED DIFFUSED	GREEN DIFFUSED
564-0100-313F	YELLOW DIFFUSED	RED DIFFUSED	YELLOW DIFFUSED
564-0100-320F	YELLOW DIFFUSED	GREEN DIFFUSED	** BLANK **
564-0100-321F	YELLOW DIFFUSED	GREEN DIFFUSED	RED DIFFUSED
564-0100-322F	YELLOW DIFFUSED	GREEN DIFFUSED	GREEN DIFFUSED
564-0100-323F	YELLOW DIFFUSED	GREEN DIFFUSED	YELLOW DIFFUSED
564-0100-331F	YELLOW DIFFUSED	YELLOW DIFFUSED	RED DIFFUSED
564-0100-332F	YELLOW DIFFUSED	YELLOW DIFFUSED	GREEN DIFFUSED
564-0100-333F	YELLOW DIFFUSED	YELLOW DIFFUSED	YELLOW DIFFUSED
564-0100-666F	WHITE WATER CLEAR	WHITE WATER CLEAR	WHITE WATER CLEAR
564-0100-700F	ORANGE DIFFUSED	** BLANK **	** BLANK **
564-0100-712F	ORANGE DIFFUSED	RED DIFFUSED	GREEN DIFFUSED
564-0100-717F	ORANGE DIFFUSED	RED DIFFUSED	ORANGE DIFFUSED
564-0100-732F	ORANGE DIFFUSED	YELLOW DIFFUSED	GREEN DIFFUSED
564-0100-772F	ORANGE DIFFUSED	ORANGE DIFFUSED	GREEN DIFFUSED
564-0100-777F	ORANGE DIFFUSED	ORANGE DIFFUSED	ORANGE DIFFUSED
*564-0100-779F	ORANGE DIFFUSED	ORANGE DIFFUSED	BLUE (WHITE DIFF. EPOXY)
*564-0100-921F	BLUE (WHITE DIFF. EPOXY)	GREEN DIFFUSED	RED DIFFUSED
*564-0100-922F	BLUE (WHITE DIFF. EPOXY)	GREEN DIFFUSED	GREEN DIFFUSED
*564-0100-923F	BLUE (WHITE DIFF. EPOXY)	GREEN DIFFUSED	YELLOW DIFFUSED
*564-0100-927F	BLUE (WHITE DIFF. EPOXY)	GREEN DIFFUSED	ORANGE DIFFUSED
*564-0100-932F	BLUE (WHITE DIFF. EPOXY)	YELLOW DIFFUSED	GREEN DIFFUSED
*564-0100-972F	BLUE (WHITE DIFF. EPOXY)	ORANGE DIFFUSED	GREEN DIFFUSED
*564-0100-999F	BLUE (WHITE DIFF. EPOXY)	BLUE (WHITE DIFF. EPOXY)	BLUE (WHITE DIFF. EPOXY)



ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES

OPERATING CHARACTERISTICS AT 25°C AMBIENT												
COLOR	LUMINOUS INTENSITY @I _F = 10 mA WHITE @I _F = 20mA (mcd)			FORWARD VOLTAGE TEST CONDITION	FORWARD VOLTAGE (V)		REVERSE CURRENT V _R = 5V	PEAK WAVELENGTH (nm)	DOMINANT WAVELEGTH (nm)			VIEWING ANGLE (DEG)
	MIN	TYP	MAX		TYP	MAX	MAX	TYP	MIN	TYP	MAX	TYP
RED	7.4	10.0	—	I _F =20mA	2.0	2.8	100 μA	635	618	623	633	60
GREEN	4.7	12.6	—	I _F =20mA	2.1	2.8	100 μA	565	564	565	573	60
YELLOW	7.4	10.0	—	I _F =20mA	2.1	2.8	100 μA	585	584	590	595	60
ORANGE	3.4	7.0	—	I _F =10mA	2.2	3.0	100 μA	600	597	602	616	60
BLUE	30	57	85	I _F =10mA	2.0	3.5	100 μA	468	460	467	475	100
WHITE	400	1100	1900	I _F =20mA	3.5	4.0	100 μA	—	—	—	—	45

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT	UNITS	RED	YELLOW	GREEN	ORANGE	BLUE	WHITE
POWER DISSIPATION	mW	100	60	100	135	120	
CONTINUOUS FORWARD CURRENT	mA	30	20	30	25	30	
DERATING LINEAR FROM 50°C (30°C FOR BLUE AND WHITE)	mA/°C	0.4	0.25	0.4	0.5	0.5	0.45
PEAK FORWARD CURRENT (t≤100μs,D=0.1)	mA	120	80	120	90	100	
SOLDERING TEMPERATURE (5 SEC, .063" FROM BODY)	°C	260					
OPERATING TEMPERATURE	°C	-55 TO +100				-25 TO +80	-40 TO +85
STORAGE TEMPERATURE	°C	-55 TO +100				-30 TO +100	-40 TO +100



SCALE 1.000

NOTES:

- LEADS TO FIT INTO HOLES SPACED AS PER HOLE PATTERN
- WHEN A ZERO APPEARS IN THE LAST 3 DIGITS OF THE PART NUMBER THIS MEANS NO LAMP IN THAT POSITION.
- LED LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
- PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PARTS.
- RED,GRN,YEL,BLUE,WHITE .018 X .016; ORANGE .018 SQ.
- TOLERANCE ON LEAD THICKNESS TO BE ±.003.

* ATTENTION: OBSERVE PRECAUTIONS FOR HANDLING
ELECTROSTATIC SENSITIVE DEVICES.

REV	REVISIONS	DRN	CKD	APP	DATE
A	NEW RELEASE	TWC	MES	NO	8-10-05
B	ADDED P/N 564-0100-922F AND ESD LOGO	TWC	TC	NO	9-25-05
C	ADDED P/N 564-0100-200F,-201F	TWC	NO	MES	2-8-06
D	ADDED P/N 564-0100-173F	TC	NO	MES	11-28-06
E	ADDED P/N 564-0100-772F	SM	MES	NO	5-25-07
F	ADDED P/N 564-0100-712F	KLJ	NO	AV	4-10-08
G	ADDED P/N 564-0100-229F; UPDATED BLUE SPECS.	KLJ	NO	MES	1-26-09
H	ADDED P/N 564-0100-217F	KLJ	NO	MES	4-2-09
J	UPDATED BLUE LED SPECS	AJF	KLJ	NO	6-20-11
K	ADDED P/N's 564-0100-102F, 209F, 219F, 717F, 732F ADDED DOMINANT WAVELENGTHS	JG	WFB	NO	4-29-13
L	ADDED LEAD THICKNESS TOLERANCE NOTE	MMB	WFB	NO	6-21-13
M	ADDED 564-0100-129F UPDATED BLUE LED SPECS	WFB	JTD	NO	10/3/14
N	ADDED 564-0100-666F	RSK	WFB	NO	11-11-14
O	UPDATED WHITE O/S TEMPS	RSK	WFB	NO	12/9/14
P	ADDED P/N 564-0100-279F/291F	BP	—	NO	10-03-16
Q	ADDED 564-0100-923F/927F	BP	—	NO	11-30-16
R	ADDED 564-0100-779F, CHANGED WHITE DIFF. LENS TO WHITE DIFF. EPOXY	LD	—	NO	3-25-19
S	ADDED 564-0100-299F	LD		NO	4-06-20
T	ADDED 564-0100-972F, "*" NOW APPLIES TO P/Ns WITH BLUE LED	LD		NO	9-17-20
U	ADDED 564-0100-921F	LD		NO	5-11-21

HUE BIN	CHROMATICITY COORDINATES FOR WHITE WATER CLEAR I _F = 20 mA			
	x	y	z	u
A3	x	0.270	0.270	0.250
	y	0.275	0.325	0.300
A4	x	0.270	0.250	0.250
	y	0.275	0.250	0.225
B3	x	0.290	0.290	0.270
	y	0.300	0.350	0.325
B4	x	0.290	0.270	0.270
	y	0.300	0.275	0.225
C3	x	0.310	0.310	0.290
	y	0.325	0.375	0.350
C4	x	0.310	0.290	0.290
	y	0.325	0.300	0.250
D3	x	0.330	0.330	0.310
	y	0.350	0.400	0.375
D4	x	0.330	0.310	0.310
	y	0.350	0.325	0.275
COLOR COORDINATES MEASUREMENT ALLOWANCE ± 0.01				

IV BIN	LUMINOUS INTENSITY (mcd), I _F = 20mA	
	MIN.	MAX.
LM	400	680
NP	680	1150
QR	1150	1900
LUMINOUS INTENSITY MEASUREMENT ALLOWANCE IS 15%		

RoHS Compliant 564-0100-XXXX Thru-hole CBI

Part Numbers with the "F" suffix ending are RoHS Compliant. Example: 564-0100-002F, 564-0100-999F
The bag packaging is marked with "RoHS Compliant" label or equivalent markings. Parts can be wave soldered, dip soldered, or hand soldered using typical lead-free soldering process with max 260°C temperature for 5 seconds.

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
SCALE: DRAWING SCALE	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-17281	U
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	MATERIAL
FRACTIONS: ±1/64	STANDARD 3X1 CBI BLOCK	RoHS COMPLIANT
DECIMALS (.XX): ±.01		
DECIMALS (.XXX): ±.005		
DECIMALS (.XXXX): ±.0005		
ANGLES: ±1°		
FINISH		
FSCM 83330		
SHEET 1 OF 1	FAMILY TABLE:	



1501 ROUTE 34 SOUTH
FARMINGDALE, NJ 07727
(732) 919-3119
www.dialight.com