




SIGN	DATE	DESCRIPTION	APPROVER
△	2009.03.31	Add the inspection dimension	Jacke
△	2010.05.30	Add cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ③ Clamp: Brass(CuZn) Ni plated
- Item ⑤ Terminal screw: Steel Zinc plating "-" slot type
- Item ⑥ Female contact: PhBz (CuSn) Tin plated
- Item ⑦ Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 14-26
- Stranded wire(AWG): 14-26
- Torque: 3.5Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature:-40°C to+115°C
- △ ● Safety Approval: cULus



KR xx 01 x 0 xxxx G

RoHS
Pb<40,000ppm

Poles	0	Black (RAL9005)	0000	Standard @ Logo
02 2Contacts	2	Red (RAL3001/D)	000A	Standard ANY Logo
02 3Contacts	3	Orange(RAL2011/P)	Any special item by	
—	4	Yellow(RAL1018/A)	customer request,	
24 24Contacts	5	Green(RAL6018/T)	please contact sales	
	6	Blue (RAL5015/A)	department.	
	8	Grey(RAL7035/D)		

N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

	Dim A	Dim B	Dim C	Dim D
2P	±0.05	±0.05	≤0.05	≤0.05
3-6p	±0.15	±0.15	≤0.10	≤0.10
7-12p	±0.20	±0.20	≤0.20	≤0.20
13-18p	±0.30	±0.30	≤0.40	≤0.40
19-24p	±0.40	±0.40	≤0.40	≤0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KR 5.0mm Series "-" (Without hook)			
PART NO.	KRxx01x0xxxxG			DWG NO.	8KR0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Jacke 2010.05.30	Jacke 2009.03.31		X. ±0.50
					X.X ±0.30
					X.XX ±0.10
				SHEET: 01/01	REV.: D