

MI DRG. NO.

57273D

REV.

57273



D

TRIMMER CAPACITOR (GIGA-TRIM®)

SPECIFICATIONS

FILE: AIROUT

CAPACITY RANGE	0.8pF TO 8.0pF (>8 TURNS)
WORKING VOLTAGE	500 VDC (1000 VDC TEST)
Q @ 100 MHz	>2000
INSULATION RESISTANCE	>10 ⁶ MEGOHMS
TEMPERATURE RANGE	-65°C TO +125°C
TORQUE	0.2 TO 2.0 OZ. IN
ROTATIONAL LIFE	50 CYCLES (400 REVOLUTIONS)
VIBRATION	15G @ 10-2000 Hz
SHOCK	100G @ 6 ms
MOISTURE RESISTANCE	10-24 HR. CYCLE
BRASS & INVAR STRUCTURE	
CERAMIC DIELECTRIC	
FINISHES: GOLD AND SILVER PLATE	
RoHS COMPLIANT	
ACTUAL SIZE	

PENETRABLE
SEAL CAP

D	02/08/10	BFH	MAI	MAI	000811
C	09/21/06	MLD	MAI	MAI	000442
B	03/06/00	-	-	-	000-077
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN.	CHK.	APP.	SCALE
RMV	TAM	JHT	4" = 1"
DATE	DATE	DATE	.XX ± .015
03/06/00	03/08/00	03/08/00	.XXX ± .005



JOHANSON MANUFACTURING CORPORATION

ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL