

PRODUCT NO.
10129885-00XLF





NOTES:

- MATERIAL:
 - HOUSING: LCP OR EQUIVALENT MATERIAL UL94V-0, BLACK
 - TERMINAL: BRASS
 - HOLD DOWN: BRASS
- FINISH:
 - TERMINAL: SEE PART NUMBER DEFINITION, NICKEL UNDER PLATING
 - HOLD DOWN: TIN OVER AREA, NICKEL UNDER PLATING
- LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIPTION IN GS-22-008
- PRODUCT SPEC: GS-12-240
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- PART NUMBER:
10129885-00XLF


LEAD FREE
CONTACT AREA:

- 3u"GOLD ON CONTACT AREA, TIN ON SOLDER TAIL
- 10u"GOLD ON CONTACT AREA, TIN ON SOLDER TAIL
- 2u"GOLD OVER ALL.
- 30u"GOLD ON CONTACT AREA, TIN ON SOLDER TAIL

ALL SOLDERING TAILS
(INCLUDE TWO SIDES HOLD DOWN)



SECTION A-A




RECOMMENDED PCB LAYOUT: COMPONENTS SIDE
TOLERANCE: ± 0.05

DIM A			
DIM	4.25	3.50	5.00
PIN NUMBER	OTHERS	25, 26	1, 13, 38, 50

spec ref	-
tolerance std	ISO 406 ISO 1101
surface	✓
linear	0.X ± 0.25 0.XX ± 0.15 0.XXX ± 0.08
angular	0° $\pm 2^\circ$

dr	Li-Qing Lei	2015/06/29
eng	Nick Zhang	2015/12/13
chr	-	-
appr	Tim Yao	2015/12/13
title	CF CARD HEADER	
www.fci.com	1.27 PITCH CF CARD SMT NORMAL TYPE	
cat. no.	-	

projection		mm 	size A3	scale 2:1
			ecn no ELX-N-22766-1	
product family			-	rel level Released
R		dwg no 10129885	rev B	
CARD SMT NORMAL TYPE				
-	Product - Customer Drw			sheet 1 of 2



Copyright FCI.

B

A

B


C

D

2

3



4




NOTES:

- 1. CARRIER TAPE MATERIAL: THERMOPLASTIC ANTI-STATIC FILM OR EQUIVALENT THICKNESS: 0.50mm; COLOR: BLCAK.
- 2. COVER TAPE MATERIAL: CONDUCTIVE COVER TAPE OR EQUIVALENT.
- 3. PLASTIC REEL MATERIAL: PS, COLOR: BLUE OR BLACK.
- 4. PEEL STRENGTH REQUIREMENT OF COVER TAPE TO COMPLY WITH EIA-481.
- 5. ALL TAPE AND SPROCKET HOLE DIMENSIONS SHOWN ARE PER EIA-481.
- 6. PACKING QUANTITY: 200 PCS PER 13" REEL; 400 PCS PER CARTON.

DIRECTION OF PULL
START



SECTION: B-B



DETAIL: C

spec ref -				dr Li-Qing Lei		2015/06/29		projection	mm	size A3		scale 2:1		
tolerance std				eng Nick Zhang		2015/12/13				ecn no ELX-N-22766-1				
ISO 406				chr -		-				rel level Released				
ISO 1101				appr Tim Yao		2015/12/13								
TOLERANCES UNLESS OTHERWISE SPECIFIED				product family				-						
surface ✓		linear	0.X		±0.25		FCi	title CF CARD HEADER				dwg no 10129885		rev B
			0.XX		±0.15									
			0.XXX		±0.08									
		angular		0°		±2°								
ISO 1302						www.fci.com		cat. no. -		Product - Customer Drw		sheet 2 of 2		

2

3

PDS: Rev :B

STATUS:Released

Printed: Dec 14, 2015