

MI DRG. NO.

2320-12GF

REV.

2320-12G F**CERA-TRIM[®] CAPACITOR**


SPECIFICATIONS

FILE: THINOUT

CAPACITY RANGE	2.5 TO 10pF
WORKING VOLTAGE	250 VDC (TEST VOLTAGE 500 VDC)
Q @100 MHz	> 1000
INSULATION RESISTANCE	> 10 ⁴ MEGOHMS
TEMPERATURE RANGE	-55°C TO +125°C
TORQUE	0.05 TO 1.0 OZ. IN.
MOISTURE RESISTANCE	MIL-STD-202, METHOD 106
SHOCK	100 g @6 ms
VIBRATION	15 g @10-2000 Hz
SETTING DRIFT	< 1%

CERAMIC DIELECTRIC STRUCTURE

GOLD PLATED TERMINALS



F	01/03/07	MLD	MAI	MAI	000479
E	09/30/02	MLD	TAM	TAM	020-085
D	04/02/02	MLD	TAM	TAM	020-026
C	03/12/02	MLD	-	-	020-018
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN.	CHK.	APP.	SCALE
MLD	TAM	JHT	4" = 1"
DATE	DATE	DATE	.XX ± .015
03/12/02	03/12/02	03/12/02	.XXX ± .005

**JOHANSON MANUFACTURING CORPORATION**

ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL