




- | | |
|---|--|
| 1 | CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .125 – TOLERANCE NON-CUMULATIVE |
| 2 | AMP LOGO MOLDED IN APPROXIMATE AREA SHOWN. |
| 3 | .000050 GOLD IN CONTACT AREA, .000100—.000200 TIN ON THE TERMINATION AREA,
ALL OVER .000050 NICKEL |
| 4 | .000030 GOLD IN CONTACT AREA, .000100—.000200 TIN ON THE TERMINATION AREA,
ALL OVER .000050 NICKEL. |



		1.868	1.750	14	30	5-5102935-7
		2.493	2.375	19	40	3-5102935-6
		1.993	1.875	15	32	2-5102935-8
		1.493	1.375	11	24	1-5102935-9
		1.243	1.125	7	20	1-5102935-6
		.993	.875	9	16	1-5102935-2
		.743	.625	5	12	5102935-8
		.618	.500	4	10	5102935-6
		.493	.375	3	8	5102935-4
		.368	.250	2	6	5102935-2
REMARKS	FINISH	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN S. BURKHOLDER 040C72004 QWK 22N0V04 M. YEOMANS M. YEOMANS 22N0V04		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 .010 ± .005 1 .010 ± .005 2 .010 ± .005 3 .010 ± .005 4 .010 ± .005 ANGLES ± .5° FINISH		NAME RECEPTACLE ASSY, LEVEL V DOUBLE ROW, .125 x .125 CL #22 - #26 Gage, LEAD FREE	
MATERIAL -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A1 CAGE CODE 00779 DRAWING NO C=5102935 RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV D	