


Rack And Panel Connectors

Features:

- 0.150" (3.81mm) contact spacing x 0.130" (3.30mm) or 0.150" (3.81mm) row spacing with staggered grid
- Plug and receptacle in 20, 38, 56, 90 and 120 contact sizes
- Edacon hermaphroditic contact mating design
- Contact termination options include crimp, P.C. tail, wire hole and wire wrap
- Mating and unmating simplified with use of actuating screws
- Optional covers with side or top entry cable clamp in plastic or metal material available for all connector sizes
- Versatile metal cover design permits assembly or disassembly after cabling is complete plus cable entry style flexibility
- Actuating screws, locknuts, polarizing hardware, covers and contacts suitable for either plug or receptacle
- Polarizing hardware adjustable for 288 mating combinations
- Tools available for contact installation, removal, crimping and polarizing changes
- RoHS Compliant & UL Certified



Specifications:

Insulator Material	Diallyl Phthalate, Thermoplastic Polyester or Polycarbonate UL 94V-0
Color	Green or Grey (For 120 Pin Only)
Contact Material	Copper Alloy
Contact Plating	Gold Plating over Nickel over entire contact
Current Rating	8.5 amps
Contact Resistance	10 milliohms maximum
Dielectric Withstanding Voltage	2000 V AC rms at sea level
Insulation Resistance	5000 megaohms minimum
Operating Temperature	-40°C to +125°C (Diallyl Phthalate Only)
Operating Temperature	-40°C to +105°C
Insertion & Withdrawal Force	2 to 16 oz (0.56 to 4.45N) per contact position

Example Part Number: 516-038-500-212

Series _____

Total Number of Contacts _____

Contact Code _____

Style and Material _____

Cover Code _____

Hardware Code _____


Series:				Cover Code:	Description:		
516				0	No Cover Assembly		
Total Number of Contacts:				1	Plastic Cover, Top Entry Standard Clamp		
020, 038, 056, 090 or 120				2	Plastic Cover, Side Entry Standard Clamp		
Contact Code:	Description:	Tail Size:	Tail Length "G":	3	Plastic Cover, Top Entry Large Clamp		
000	No Contacts Assembled	-----	-----	4	Plastic Cover, Side Entry Large Clamp		
500	Wire Hole	.110 x .024 (2.79 x 0.61)	.245 (6.22)	5	Metal Cover, Side Entry		
501	Taper Tail	.110 x .024 (2.79 x 0.61)	.245 (6.22)	6	Metal Cover, Top Entry		
520	P.C. Tail	.025 x .024 (0.64 x 0.61)	.215 (5.46)	Hardware Code:	Description:		
540	Wire Wrap	.050 x .024 (1.27 x 0.61)	.600 (15.24)	0	No Hardware		
541	Wire Wrap	.026 x .024 (0.66 x 0.61)	.620 (15.70)	1	Actuating Screw & Polarizing Hardware		
542	Wire Wrap	.050 x .024 (1.27 x 0.61)	.790 (20.07)	2	Locknut & Polarizing Hardware		
Style & Material:	Style:	Insulator Material:					
1	Plug	Green Diallyl Phthalate	5	Actuating Screw with No Polarizing Hardware			
2	Receptacle	Green Diallyl Phthalate	6	Locknut with No Polarizing Hardware			
3	Plug	Grey Polycarbonate					
4	Receptacle	Grey Polycarbonate					
5	Plug	Green Polyester					
6	Receptacle	Green Polyester					

Rack And Panel Connectors

Ordering Code Notes:

1) Crimp contacts are also available for 516 series connectors. Contacts may be ordered separately for pre-wired or select position assembly.

Part Number	Description	Silhouette
516-290-500	Wire Hole	
516-290-501	Taper Tail	
516-290-520	P.C. Tail	
516-290-540	Wire Wrap	
516-290-541	Wire Wrap	
516-290-542	Wire Wrap	
516-290-590	Crimp (Loose)	
516-294-571	Crimp - 1800 Contact Per Reel	



- For contact installation, removal and crimping tools, please contact EDAC.
- Grey Polycarbonate and Polyester insulator material is not available for 120 pin size connector. 120 pin size connector can only be supplied in DAP (Green and Grey). 120 pin part number ends with 3XX or 4XX are supplied in grey DAP.
- 20 pin connector cover will not accept the length of the wire wrap contacts
- Plastic covers with large clamps are only available for 38 and 56 pin sizes only
- Metal covers with side entry may be converted to top entry by removing side plate and changing clamp orientation
- Covers may be ordered separately
- Insulator design prevents improper mating of individual plug and receptacle. Polarizing hardware enables specific plug and receptacle combinations

Crimp Characteristics

- Contacts and Crimp Tool Accommodate from 28AWG to 18AWG, Solid or Stranded Conductor Diameters from .012 (0.30) to .049 (1.25) and an Insulation diameter up to 0.074 (1.88)
- Multiple Smaller Gauge Wires may be Crimped Together
- Crimp Resistance from 0.5 Milliohms (18AWG) to 1.5 Milliohms(28AWG)
- Crimp Tensile Strength for Wire Sizes:
 - 18AWG - 40 lbs (178 N)
 - 20AWG - 25 lbs (111 N)
 - 22AWG - 15 lbs (67 N)
 - 24AWG - 10 lbs (44 N)
 - 26AWG - 5 lbs (22 N)
 - 28AWG - 3 lbs (13 N)

Polarizing Codes

- Polarizing Hardware Changes allow 288 Mating Combinations
- Standard Code Supplied for Plugs PG1G1, for Receptacle RS1S1.
- Connectors with Special Polarizing Codes Available upon Special Request

Example Polarizing Code:

P G 4 S 2

Type of Connector _____
P - Plug, R - Receptacle

Large Diameter Hardware _____
G - Guidepin (at Contact Position "A" end)
H - Guidepin (at Last Contact Position end)
S - Socket (at Contact Position "A" end)
T - Socket (at Last Contact Position end)


Position of large Diameter Keyway - 1 Through 6 _____

Small Diameter Hardware (Opposite end From Large Diameter) _____
G - Guidepin, S - Socket


Position of Small Diameter Keyway - 1 Through 6 _____

This Example mates with Code RS4G2


TYPICAL PLUG WITH ACTUATING SCREW AND POLARIZING GUIDE PINS




TYPICAL RECEPTACLE WITH LOCKNUT AND POLARIZING SOCKETS



TYPICAL PLUG WITH ACTUATING SCREW, POLARIZING GUIDE PINS AND COVER




TYPICAL RECEPTACLE WITH LOCKNUT, POLARIZING SOCKETS AND COVER




CONNECTOR MATING FACE VIEWS

DIMENSIONS INDICATED FOR EACH SIZE APPLY TO BOTH PLUG AND RECEPTACLE


20 PIN PLUG




20 PIN RECEPTACLE




38 PIN PLUG




38 PIN RECEPTACLE




56 PIN PLUG




56 PIN RECEPTACLE




90 PIN PLUG



90 PIN RECEPTACLE



120 PIN PLUG



120 PIN RECEPTACLE

