




NOTES:

- METALSHELLS: STEEL; min. $315\mu\text{in}$ TIN over $40-80\mu\text{in}$ NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- NO CONTACT ON POS. A1
- THREADED INSERTS: COPPER ALLOY; min. $200\mu\text{in}$ TIN over $80\mu\text{in}$ NICKEL
- COLLARS: COPPER ALLOY; min. $200\mu\text{in}$ TIN over $80\mu\text{in}$ NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3021W1PAM99A30X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)					
							material: SEE NOTES					
								date	name	title: D-SUB COMBINATION MALE 21W1P SOLDER CUP with threaded insert		
								drawn	11.11.13			
				appd.	13.11.13	Lehmenkühler						
						norm	dwg no:					
						d-old				DIN-A3		
	a	Original						13K1A4514				
								sh: 1				
	rev.	description	date	name				part no: 3021W1PAM99A30X				