







N = Number of poles

Dim.A	$N \times 7.62$
Dim.B	$(N-1) \times 7.62$
Dim.C	$(N+1) \times 7.62$
Dim.D	$(N+2) \times 7.62$

Dimension

Poles	Tolerance
2P-5P	± 0.20
6P-10P	± 0.30
11P-16P	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ③ Terminal(housing) : PA66 (UL94V-0)
- Item ④ Terminal(cover) : PA66 (UL94V-0) (ET 7.62)
- Item ⑤ Terminal screw : Steel Zinc plating " - " slot type (ET 7.62)
- Item ⑥ Clamp : Brass, Ni plated (ET 7.62)
- Item ⑦ Female contact : Copper, Tin plated
- Item ⑧ With flange Nut : Steel Zinc plating M3 (VC 7.62)

Electrical

- Voltage rating: 600VAC
- Current rating: 41A
- Solid wire (AWG): 8-24
- Stranded wire(AWG): 8-24
- Torque: 9.0 Lb-In
- Screw: M3.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

- Critical dimension: 

K T xx 0 1 x 2 xxxx G

No. OF POLES
02: 2 POLES
...
16: 16 POLES

COLOR

- 0 Black (RAL9005)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- C Green(RAL6018/U)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KT 7.62 Series 2P-16P " - " Screw (Flange With Nut)						
PART NO.	KTxx01x2xxxxG			DWG NO.	8KT0014		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Aaron 2011.10.18	Aaron 2011.10.18			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: B		X.XX ±0.10
							X° ±1°