





REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN I APVD
M		REVISED	PER	ECO 20-005651	8-11-20	CT DM



- .040 DIA HOLE IS RECOMMENED FOR P.C. BOARD
- CONNECTOR MATES WITH ANY AMP 44 POSN RECEPTACLE
- REPLACEMENT PIN AMP# 207683-8
- UL/CSA DESIGNATION STAMPED IN THIS AREA.
- CLINCH NUT(QTY = 2) IS USED ON 208868-3 ONLY.
- FINISH: CADMIUM PER QQ-P-416
- FINISH: ZINC PLATED PER ASTM-B-633, .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+)

PLATED PER 7	5-208868-1
5, PLATED PER 6	208868-3
PLATED PER 6	208868-2
PLATED PER 6	208868-1
DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 1-7-88	TE Connectivity	
DIMENSIONS: INCHES		CHK F.C.BALLEW III 1-26-88		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.C.BALLEW III 1-26-88	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	PRODUCT SPEC APPLICATION SPEC		
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT 0.000000	SIZE A1	RESTRICTED TO
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV M