




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECO-16-008038	27MAY2016	NK	JO
	H	REVISED PER ECO-18-012301	06AUG2018	RS	JO






- 1 HOUSING: HIGH TEMPERATURE, GLASS FILLED NYLON, COLOR: BLACK.
CONTACTS: PHOSPHOR BRONZE.
- 2 CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254 BRIGHT TIN-LEAD ON REMAINDER, ALL OVER 0.001270 NICKEL.
- 3 PCB HOLE RECOMMENDATIONS:
A. DRILL HOLE DIAMETER TO BE 1.00±0.02.
B. PLATING TO BE 0.005 MIN TIN-LEAD OVER 0.025-0.075 COPPER.
C. RECOMMENDED FINISH HOLE SIZE IS 0.88±0.08.
- 4 DIMENSION AFTER SEATING TO PCB.
- 5 NO CONTACT IN THIS POSITION FOR 1375800-2 & -5 ONLY.
- 6 NO CONTACT IN THIS POSITION FOR 1375800-3 & -6 ONLY.
- 7 CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254-0.00508 MATTE TIN ON REMAINDER, ALL OVER 0.001270 NICKEL.
- 8 TO BE USED ON SILVER IMMERSION PLATED PCB'S (NOTE 9).
- 9 PCB HOLE RECOMMENDATIONS FOR SILVER IMMERSION PLATING:
A. DRILL HOLE DIAMETER TO BE 1.00-1.02.
B. PLATING TO BE 0.0001524-0.0004064 SILVER OVER 0.0508±0.0254 COPPER.
C. RECOMMENDED FINISH HOLE SIZE IS 0.94-0.97.
- 10 PCB HOLE RECOMMENDATIONS FOR ENIG PLATING:
A. DRILL HOLE DIAMETER TO BE 1.00-1.02.
B. PLATING TO BE 0.000051-0.000127 GOLD OVER 0.00305-0.00610 NICKEL ALL OVER 0.0508±0.0254 COPPER.
C. RECOMMENDED FINISH HOLE SIZE IS 0.94-0.97.
- 11 TO BE USED ON STANDARD PCB (NOTE 3) OR ENIG PLATED PCB (NOTE 10).
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



8	7	YES 6	1375800-6
8	7	YES 5	1375800-5
8	7	NO	1375800-4
11	2	YES 6	1375800-3
SUPERCEDED BY 1375800-5		YES 5	1375800-2
11	2	NO	1375800-1
FINISH		KEYED CIRCUIT	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN W.G.LENKER CHK L.BREKOSKY APVD J.OLSON	20JUN2000 15JAN2001 13JUN2001	TE Connectivity		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	ASSEMBLY, PC/104-PLUS, NON-STACKTHROUGH CONTACTS, PRESS FIT		
mm		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ±		PRODUCT SPEC			
		ANGLES ±		APPLICATION SPEC			
MATERIAL		FINISH		WEIGHT			
1		2 7		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2
						REV H	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G.LENKER CHK L.BREKOSKY APVD J.OLSON		20JUN2000 15JAN2001 13JUN2001		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		ASSEMBLY, PC/104-PLUS, NON-STACKTHROUGH CONTACTS, PRESS FIT	
		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-1956 APPLICATION SPEC 114-13021			
MATERIAL		WEIGHT		SIZE		CAGE CODE	
		-		A1		00779	
CUSTOMER DRAWING		DRAWING NO		DRAWING NO		RESTRICTED TO	
				C=1375800			
		SCALE		99:20		SHEET 2 OF 2 REV H	