



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	1997
© COPYRIGHT 1997	ALL RIGHTS RESERVED.	

PN 1-1,2-1,3-1,4-1,5-1,1-2,2-2,3-2
4-2,5-2,6-1,4-3,1-8,2-8,3-8,4-8,5-8,
4-9,2-9,3-9,4-9 & 5-9



PN 1-1,2-1,3-1,4-1,5-1,1-2,2-2,3-2
4-2,5-2,6-1,4-3,1-8,2-8,3-8,4-8,5-8,
4-9,2-9,3-9,4-9 & 5-9



NOTES

- 1 MATERIAL SEE TABLE
- 2 SURFACE SEE TABLE
- 3 ASSEMBLY WEIGHT SEE TABLE
- 4 PACKAGING: 50 PIECES IN POLY-BAG 0-1243085-8
- 5 PACKAGING: 500 PIECES IN POLY-BAG 0-1243085-8
- 6 PACKAGING: 10 PIECES IN POLY-BAG 0-1243085-8
- 7 CROSS-SECTION MARKING

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B13	Released As per ECR-09-005436	9-Mar-2009	CJ	TS
			B14	ECR-11-002636	05APR2011	SR	AR
			B15	REVISED PER ECR-16-016780	19AUG2017	NG	MKO

													 SCALE 4:1									
OB SO LE TE	OB SO LE TE	OB SO LE TE								OB SO LE TE												
1	1	1	1	1	1	1	1	1	1	1	1	1	3	1	2				7	2		
1	1	1											Catch Spring		Stainless Steel							
		1											Pin Contact 1.5 mm ²	0.00062	Ms/Brass	Ag/Ni	1.8	3.0	4			
													Pin Contact 4.0 mm ²	0.00059	Ms/Brass	Ag/Ni	2.4	3.2	6			
				1									Pin Contact 2.5 mm ²	0.00067	Ms/Brass	Au	2.2	3.2	5			
					1								Pin Contact 1.5 mm ²	0.00067	Ms/Brass	Au	1.8	3.0	4			
						1							Pin Contact 0.75-10 mm ²	0.00063	Ms/Brass	Au	1.45	2.6	3			
							1						Pin Contact 0.5 mm ²	0.00062	Ms/Brass	Au	1.1	2.6	2			
								1					Pin Contact 0.14-0.37 mm ²	0.00061	Ms/Brass	Au	0.9	2.6	1			
									1				Pin Contact 2.5 mm ²	0.00065	Ms/Brass	Ag/Cu	2.2	3.2	5	1		
										1			Pin Contact 1.5 mm ²	0.00067	Ms/Brass	Ag/Cu	1.8	3.0	4			
											1		Pin Contact 0.75-10 mm ²	0.00063	Ms/Brass	Ag/Cu	1.45	2.6	3			
												1	Pin Contact 0.5 mm ²	0.00062	Ms/Brass	Ag/Cu	1.1	2.6	2			
OB SO LE TE		1											Pin Contact 0.14-0.37 mm ²	0.00061	Ms/Brass		0.9	2.6	1			
OB SO LE TE			1										Pin Contact 0.14-0.37 mm ²	0.00065	Fe	Au	0.9	2.6	1			
												1	Pin Contact 0.14-0.37 mm ²	0.00067	Ms/Brass	Ag/Cu	0.9	2.6	1			

4	4	6	6	4	4	4	4	4	4	4	4	4	4	DESCRIPTION	WEIGHT IN (Kg)	MATERIAL	SURFACE	ØA	ØB	CROSS SECTION MARKING	POS
4-3	6+1	1-4	1-3	5-2	4-2	3-2	2-2	1-2	5-1	4-1	3-1	2-1	1-1								
				5	5	5	5	5	5	5	5	5	5								
				5-9	4-9	3-9	2-9	1-9	5-8	4-8	3-8	2-8	1-8								

HN.D-C-Sti.Ag/Ni.1.5 mm ²	
HN.D-C-Sti.Ag/Ni.4.0 mm ²	
HN.D-C-Sti.Cu/Ni.0.14 -0.37 mm ²	
HN.D-C-Sti.Fe.Au.0.14 -0.37 mm ²	
HN.D-C-Sti.Au.2.5 mm ²	
HN.D-C-Sti.Au.1.5 mm ²	
HN.D-C-Sti.Au.0.75-1.00 mm ²	
HN.D-C-Sti.Au.0.5 mm ²	
HN.D-C-Sti.Au.0.14 -0.37 mm ²	
HN.D-C-Sti.Ag.2.5 mm ²	
HN.D-C-Sti.Ag.1.5 mm ²	
HN.D-C-Sti.Ag.0.75-1.00 mm ²	
HN.D-C-Sti.Ag.0.5 mm ²	
HN.D-C-Sti.Ag.0.14 -0.37 mm ²	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Braun 23.07.1997 CHK Schnurpfeil 23.07.1997		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8079 DIN ISO 2768 mH-K DIN ISO 15001-20		APVD -		NAME PIN CONTACT SERIES HN.D -	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC 108-74018 APPLICATION SPEC 114-74015		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL  -		FINISH  -		WEIGHT -		A2 00779 C=1105050 -	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 OF 1 REV B15	