






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				AE	OBS -2 PER 0G3A-0533-00	01MAR01	JR/DD

- 1 CONTINUOUS STRIP ON REELS
- 2 60373-4 IS REVERSE REELED.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

OBSOLETE	2	.048-.071 DIA	24-20 AWG	60373-4
		.048-.071 DIA	24 20 AWG	60373 2

F	.080	.150	F	.062	.046	20
					.043	22
					.040	24
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR 4/24/90 P FORTNEY CHK 4/24/90 JR RUTH APPD 4/24/90 G YETTER
MATERIAL #4 HARD PHOS BRONZE	APPD 4/24/90 R KUZO PRODUCT SPEC —
FINISH .000080 MIN TIN PL	APPLICATION SPEC — WEIGHT —