


JMC P/N	CAPACITANCE	Q @ 100 MHz	COLOR CODE
2320-0	0.6 TO 2.5 pF	> 3000	RED
2320-1	1.0 TO 5.0 pF	> 1000	BLACK
2320-2	2.5 TO 10 pF	> 1000	BLUE
2320-3	5.0 TO 18 pF	> 500	GREEN
2320-4	6.5 TO 25 pF	> 300	AMBER



MI DRG. NO.

2320K

REV.

2320**K****CERA-TRIM[®] CAPACITOR**

SPECIFICATIONS		FILE: THINOUT
CAPACITY RANGE	SEE TABLE	
WORKING VOLTAGE	250 VDC (TEST VOLTAGE 500 VDC)	
Q @100 MHz	SEE TABLE	
INSULATION RESISTANCE	> 10 ⁴ MEGOHMS	
TEMPERATURE RANGE	-55°C TO +125°C	
TORQUE	0.05 TO 1.0 OZ. IN.	
MOISTURE RESISTANCE	MIL-STD-202, METHOD 106	
SHOCK	100 g @6 ms	
VIBRATION	15 g @10-2000 Hz	
SETTING DRIFT	< 1%	
CERAMIC DIELECTRIC STRUCTURE		
SOLDER FINISH TERMINALS		

K	10/07/10	NK	MAI	MAI	000870
J	01/02/07	MLD	MAI	MAI	000479
H	08/31/05	MLD	MAI	MAI	000265
G	09/30/02	MLD	TAM	TAM	020-085
F	03/16/00	-	-	-	000-108
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN. TAM	CHK. TAM	APP. JHT	SCALE 4" = 1"
DATE 03/16/00	DATE 03/16/00	DATE 03/16/00	.XX ± .015 .XXX ± .005

**JOHANSON MANUFACTURING CORPORATION**

ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION

PROPRIETARY INFORMATION CONTAINED NOT TO BE USED WITHOUT JOHANSON MANUFACTURING CORPORATION APPROVAL