





Recommand PCB layout


SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating: 2A, AC/DC
- Withstanding Voltage:800VAC/minute
- Insulation resistance:1,000MΩ min
- Temperature range:−40°C to +105 °C
- Contact resistance:20mΩ max

WAFER



- Poles:2-16
- Material: PA66 UL 94V-2
- Contact: COPPER NEEDLS H65
- Contact Plating: Tin
- Q' TY: 500/1000 pcs/Tape/reel



Poles	PART NO	DIMENSION (mm)		
		A	B	C
2	CS-1125R-02KV2RT (0010)	2.00	6.00	5.00
3	CS-1125R-03KV2RT (0010)	4.00	8.00	7.00
4	CS-1125R-04KV2RT (0010)	6.00	10.00	9.00
5	CS-1125R-05KV2RT (0010)	8.00	12.00	11.00
6	CS-1125R-06KV2RT (0010)	10.00	14.00	13.00
7	CS-1125R-07KV2RT (0010)	12.00	16.00	15.00
8	CS-1125R-08KV2RT (0010)	14.00	18.00	17.00
9	CS-1125R-09KV2RT (0010)	16.00	20.00	19.00
10	CS-1125R-10KV2RT (0010)	18.00	22.00	21.00
11	CS-1125R-11KV2RT (0010)	20.00	24.00	23.00
12	CS-1125R-12KV2RT (0010)	22.00	26.00	25.00
13	CS-1125R-13KV2RT (0010)	24.00	28.00	27.00
14	CS-1125R-14KV2RT (0010)	26.00	30.00	29.00
15	CS-1125R-15KV2RT (0010)	28.00	32.00	31.00
16	CS-1125R-16KV2RT (0010)	30.00	34.00	33.00

RoHS 2.0

类别	WAFER	品名	CS-1125R-03KV2RT (0010)	X.	±0.50	材料	颜色	单位	mm	SHEET	
										1	OF 1
										修改内容	修改日期
版本	A/0	设计	李文畅	X.X	±0.20	画法		数量	1:1		
制定部门	工程课	绘制	李文畅	X.XX	±0.10						
工程图号	CS-1125R-XX	审核	姚培柱	X.XXX	±0.05						
制定日期	2017-10-18	核准	周中湖	X.XXXX	±0.01						

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.



深圳市永丰盈电子有限公司
ShenZhenYongFengYing ELECTRONICS CO., LTD.

RoHS 2.0