




Certifications & Ratings


- RoHS and REACH compliant

Features & Benefits

- Compatible with automatic placement equipment.
- Packaged in 16mm tape, 7" reel (400 pcs/reel) and 13" reel (1600 pcs/reel).
- Compatible with surface mount reflow soldering processes.
- Housing material meets UL-94V-0 flammability ratings.
- Design provides increased indication without increased space.
- Packaged in moisture barrier bags for dry packaging per IPC/JEDEC J-STD-033.
- Helps eliminate mixed technology PC board processing.
- MSL2 for 2mA, MSL3 for 20mA

Dimensions


inches [mm]




Part Number Guide

5	9	4	-	2	X	X	X	-	0	X	X	F
Color					Current		Packaging Option					
Red	0	0		1	20mA	0	7	7" reel / 400 pcs				
Orange	5	0		1		1	3	13" reel / 1600 pcs				
Yellow	4	0		1								
Yellow-Green	3	0		1								
Green	9	0		1								
Red	0	0		4	2mA							
Orange	5	0		4								
Yellow	4	0		4								
Blue	6	0		1	20mA							
White	8	0		1	20mA							


Tape and Reel




13" Reel



7" Reel



Soldering Pad Layout



Reflow profiles shown on reverse >



Electrical/Optical Characteristics

Electrical/Optical Characteristics				Luminous Intensity (mcd)	Dominant Wavelength (nm)		Forward Voltage (V)		Viewing Angle (°deg.)	Reverse Current Intensity (μA)	
		Emitted Color	Material	If = 2.0mA							
7" Reel, 400 pcs	13" Reel, 1600 pcs			Typ	Min	Typ	Max	Typ			Max
594-2001-007F	594-2001-013F	● Red	AlInGaP	54	—	625	—	1.8	2.4	120	10
594-2501-007F	594-2501-013F	● Orange		38	—	605	—	1.8	2.4		
594-2401-007F	594-2401-013F	● Yellow		48	—	590	—	1.8	2.4		
594-2301-007F	594-2301-013F	● Yellow-Green		9	—	570	—	1.8	2.4		
594-2901-007F	594-2901-013F	● Green	InGaN	312	—	525	—	2.8	3.5		


				If = 2 mA						120	10
594-2004-007F	594-2004-013F	● Red	AlInGaP	2	624	630	635	1.7	2.2		
594-2404-007F	594-2404-013F	● Orange		3	600	606	609	1.7	2.2		
594-2504-007F	594-2504-013F	● Yellow		2.2	580	587	595	1.7	2.2		
				If = 10 mA							
594-2601-007F	594-2601-013F	● Blue	InGaN	50	465	470	475	2.5	3.1		
594-2801-007NF	594-2801-013NF	○ White		100	x=0.297 y=0.292			2.8	3.3		

Absolute Maximum Ratings

@ Ts = 25 °C

@ Ts= 25 °C	If = 20 mA		If = 2 mA	
Power Dissipation (mW)	●R, ●Y, ●YG	48	—	
	●O	60		
	○W	62		
	●G, ●B	70		
Forward Current (mA)	all	20	●R, ●O, ●Y	20
Peak Pulse Fwd Current (mA)	●R, ●Y, ●YG, ●G, ●B, ○W	100	●R, ●O, ●Y	100
	●O	80		
Reverse Voltage (V)	all	5	●R, ●O, ●Y	12
Operating Temp (°C)	-40°C to +85°C		-40°C to +100°C	
Storage Temp (°C)	-40°C to +100°C			
Electrostatic Discharge (V)	2000			

Reflow Profile



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.