


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		INITIAL RELEASE	2024.07.13	阿 树






■SPECIFICATIONS

- Voltage rating:250V AC,DC
- Current rating:3A,AC,DC
- Withstanding Voltage:800V AC/minute
- Insulation resistance:1000MQ min
- Temperature range:-45°C+95°C
- Contact resistance:20mΩ max

PART NO.:

K 202820 W V-2xXX S-NO SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① K:XKNTEK-Car Connector
- ② XKB Series No
- ③ Category:W-Wafer
- ④ Welding Board Angle:V-Stright 180°
- ⑤ Row No.-Pin No:2xXX-2x04P~2x21P
- ⑥ S-With registrarion mast;
blank-without registration
- ⑦ Material:NO-PA66 UL 94V-0
- ⑧ Plating Gategory: SN-Tin-Plated



P.C.B LAYOUT

Poles	Dimension mn	
	A	B
2x04	6.00	10.00
2x05	8.00	12.00
2x06	10.00	14.00
2x07	12.00	16.00
2x08	14.00	18.00
2x09	16.00	20.00
2x10	18.00	22.00
2x11	20.00	24.00
2x12	22.00	26.00
2x13	24.00	28.00
2x14	26.00	30.00
2x15	28.00	32.00
2x16	30.00	34.00
2x17	32.00	36.00
2x18	34.00	38.00
2x19	36.00	40.00
2x20	38.00	42.00
2x21	40.00	44.00

K202820WV-2xXXS-NOSN	PA66	Brass	Tin-Plated	K202820H
PART NO	Material	Material (pin)	Flinish(pin)	Suitable XKB Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 2.00mm Automobile Connector		
PART NO.: K202820WV-2xXXS-NOSN		
DWG NO.:		
SCALE N/A	PAGE 1/1	REVISION A1