








RoHs



CIRCUIT DIAGRAM



PCB.WELDING DRAWING

The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min

TS5061C-411-AA

按力码 按力可定制
100=10
150=15
280=28

高度码
H1. 8=018
H2. 0=020
H2. 5=025

F	按钮	LCP	1	黑色
E	盖板	不锈钢	1	清洗
D	防尘胶	聚酰亚胺	1	橙黄色
C	弹片	不锈钢	2	镀银
B	本体	LCP	1	黑色
A	卡件	磷铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.35	X.°	±5°
.XX	±0.25	X.X°	±3°
.XXX	±0.15	X.XX°	±1°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO. TS5061C-411-AA		TITLE: 3X6 DIP TACT SWITCH		
DESIGN: <i>James</i>		SIZE A4	UNITS MM	
CHED: <i>Talen</i>		SCALE	SHEET	
APPD: <i>Sophia</i>		N:A	1/1	