

SPECIFICATIONS




- Voltage rating: 250V AC/DC
- Current rating: 2A, AC/DC
- Withstanding Voltage: 800V AC/minute
- Insulation resistance: 1, 000M Ω min
- Temperature range: -40°C to +105 °C
- Contact resistance: 20m Ω max

WAFER


- Part No:CS-1261R-05
- Poles:2-16
- Material:LCP UL94V-0
- Pin:Cooper needs (H65),

Tin Plated(镀高温锡)

- Q' TY:500 pcs/Tape&reel
- Glow-wire 750°C temperature (灼热丝温度750°C)



SECTION: A-A



POLE	PART NO	DIMENSION (mm)			POLE	PART NO	DIMENSION (mm)		
		Top	entry	type			A	B	C
2	CS-1261R-02	8.0	4.8	2.0	10	CS-1261R-10	24.0	20.8	18.0
3	CS-1261R-03	10.0	6.8	4.0	11	CS-1261R-11	26.0	22.8	20.0
4	CS-1261R-04	12.0	8.8	6.0	12	CS-1261R-12	28.0	24.8	22.0
5	CS-1261R-05	14.0	10.8	8.0	13	CS-1261R-13	30.0	26.8	24.0
6	CS-1261R-06	16.0	12.8	10.0	14	CS-1261R-14	32.0	28.8	26.0
7	CS-1261R-07	18.0	14.8	12.0	15	CS-1261R-15	34.0	30.8	28.0
8	CS-1261R-08	20.0	16.8	14.0	16	CS-1261R-16	36.0	32.8	30.0
9	CS-1261R-09	22.0	18.8	16.0					

POLES 20

RoHS 2.0

本圖紙知識產權及版權由永豐盈電子有限公司所有，未經書面許可不得擅自傳閱、複製和修改。本公司保留法律追究的權利。

SORT	WAFER	PART NO.	CS-1261R-05	X.	±0.50	MATERIAL		UNIT	mm	SHEET 1 OF 1		
VERSION	A/0	DESIGNER	李文畅	X. X	±0.30	RIGIDITY		SCALE	1:1		REVISE	REVISE DATE
FRAME	工程课	DRAW BY	李文畅	X. XX	±0.20	PROJECTION		QUANTITY				
DRAWING NO.	CST-1261R	CHECK BY	YAO PEI ZHU	X. XXX	±0.10	CST 深圳市永豐盈电子有限公司 ShenzhenYongFengYing ELECTRONICS CO., LTD.						
DATE	2019-07-23	APPROVE	ZHOU ZHONG HU	X. XXXX	±0.05							

CST

深圳市永豐盈電子有限公司
ShenzhenYongFengYing ELECTRONICS CO., LTD.

	REVISE	REVISE DATE
		
		
		
		