





P.C.B LAYOUT



SECTION P-P



SECTION Q-Q

SIGN	DATE	DESCRIPTION	APPROVER
△	7/23'08	With flange type is changed	Marvin
△	7/23'08	Operating temperature is changed	Marvin
△	04/20'09	The design is changed	Jacke
△	11/17'09	The design is changed from the round hole to hexagonal hole	Jacke
△	01/12'10	Add cULus standard	Jacke
△	03/31'10	Add the 2p mark	Jacke
△	04/28'12	Flange Nut is changed	Guoxue
△	04/28'12	Add the cutaway view	Guoxue
△	04/28'12	The dimensions are added	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Materials

Item a Terminal housing:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn),Tin plated

Item c Terminal cover:Thermoplastic (UL94V-0)

Item d Flange Nut:Brass M2.5

Electrical

● Voltage rating: 300VAC

● Current rating: 10A

● Withstanding Voltage: 1.6kv

△ Operating temperature: -40°C to +115°C

● Soldering temperature: 250°C±10°C/5 Sec

△ Safety Approval: cULus

● Critical dimension:

V7 xx 7 2 x 0 xxxx G

No. OF POLES

02 2 POLES

03 3 POLES

... ..

24 24 POLES

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by

customer request.

please contact sales

department.

(N= Number of poles)

	DIM	TOL			
		2P-6P	7P-12P	13P-18P	19P-24P
△ Dim L	N×5.0+10.0	±0.15	±0.20	±0.25	±0.30
△ Dim A	N×5.0	±0.15	±0.20	±0.25	±0.30
△ Dim B	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30
△ Dim C	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30
△ Dim D	(N-1)×5.0+10.4	±0.15	±0.20	±0.25	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 5.0 Series Vertical (With flange)			
PART NO.	V7xx72x0xxxxG			DWG NO.	8V70204
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2012.04.28	Guoxue 2012.04.28		
SHEET: 01/01				UNIT: mm	X. ±0.5
				SCALE: NONE	X.X ±0.3
				REV.: H	X.XX ±0.1
					X° ±1°