

FEATURES


- Maximum output current I_{OM} : 0.1A
- Output voltage V_o : -5 V
- Continuous total dissipation P_D : 0.5 W
- Encapsulate SOT-89-3L

SOT-89-3L

1. GND

2. IN

3. OUT




ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)

Parameter	Symbol	Value	Units
Input Voltage	V_i	-30	V
Operating Junction Temperature Range	T_{OPR}	0~+150	°C
Storage Temperature Range	T_{STG}	-55~+150	°C

ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE ($V_i=-10V, I_o=40mA, C_i=0.33\mu F, C_o=0.1\mu F$, unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	25°C	-4.8	-5.0	-5.2	V
		-7V≤ V_i ≤-20V, $I_o=1mA\sim 40mA$	-4.75	-5.0	-5.25	V
		$I_o=1mA\sim 70mA$	-4.75	-5.0	-5.25	V
Load Regulation	ΔV_o	$I_o=1mA\sim 100mA$	25°C	20	60	mV
		$I_o=1mA\sim 40mA$	25°C	10	30	mV
Line Regulation	ΔV_o	-7V≤ V_i ≤-20V	25°C	15	150	mV
		-8V≤ V_i ≤-20V	25°C	12	100	mV
Quiescent Current	I_q	25°C			6	mA
Quiescent Current Change	ΔI_q	-8V≤ V_i ≤-20V	0-125°C		1.5	mA
	ΔI_q	1mA≤ V_i ≤40mA	0-125°C		0.1	mA
Output Noise Voltage	V_N	10Hz≤f≤100KHz	25°C	40		μV
Ripple Rejection	RR	-8V≤ V_i ≤-18V, f=120Hz	0-125°C	41	49	dB
Dropout Voltage	V_d	25°C		1.7		V

TYPICAL APPLICATION



Note : Bypass capacitors are recommended for optimum stability and transient response and should be located as close as Possible to the regulators.