

Wire Wound Type Common Mode Filter


- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.DCM3532F2SF series realizes small size and low profile. 3.5x3.2x2.2 mm
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.




Electrical Specifications @25°C

Part Number	Inductance 100KHz (uH)	DC Resistance (Ω) max.	Rated Current (mA)	Rated Volt (Vdc)	IR (Ω) min.
DCM3532F2SF-800T02 H	75-160	1.3	200	50	10

MECHANICAL




SUGGEST LAYOUT




Dimension: mm


SCHEMATICS



IMPEDEANCE FREQUENCY




TAPING AND PACKING



IND1752-J-E

Quantity (pcs):
2000 PCS PER REEL
16 REELS PER CARTON
32000 PCS PER CARTON

Reel



Dimensions in mm