









额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	$\leq 100\text{m}\Omega$
按力 Operating force	$\pm 50\text{gf}$
行程 Travel	$0.30 \pm 0.15\text{mm}$
绝缘电阻 Insulated resistance	$\geq 100\text{M}\Omega$
介电强度 Dielectric strength	$\geq 250\text{VAC/1mi}$

HB	4	B	050	*	1	1	0
└─	└─	└─	└─	└─	└─	└─	└─
Ⓐ	Ⓑ	Ⓒ	Ⓓ	Ⓔ	Ⓕ	Ⓖ	Ⓗ

A. 系列:HB-6*6mm系列
B. 贴装方式:4-立式贴片
C. 规格:B-4P
D. 操作高度:050-5.0mm
E. 操作力度:1-180/2-260gf
F. 操作寿命:1-100,000次
G. 固定方式:1-无柱
H. 模具编码:0-HB01



PCB. 焊接图




电路图
CIRCUIT DIAGRAM

G	按钮	PPA	1	红色
F	盖板	黄铜	1	镀铜锡
E	防水膜	硅胶	1	黑色
D	防尘膜	聚酰亚胺		橙黄色
C	弹片	磷铜/不锈钢	1	覆银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR

			GENERAL TOLERANCE	
			$\geq 0 \sim 2 <$	± 0.15
DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	± 0.25
CHECKED	ZHENGJULIAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	± 0.35

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.

WWW.KKK-JP.COM

TITLE:

6.0*6.0*5 mm 拉伸盖 SMT

of DWG NO: HB4B-H001

PART NO: HB4B20300

MODEL NO:	HB4B050-*-110
-----------	---------------

NAME:

TACT SWITCH

SAMZO COMPONENTS
Electronic switch and connector manufacturer