

5




4

3


2

1

Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802



Printed board layout
component side



09 65 322 6801	M3	2			
09 65 322 7801	M3	3			
09 65 322 5801	M3	0.76 µm Au			
09 65 322 6802	4-40 UNC	2	29773	18-APR-02	CV
09 65 322 7802	4-40 UNC	3	29689	02/07/01	AA
09 65 322 5802	4-40 UNC	0.76 µm Au	27960	13/dec/00	ALSPACE
Part number	Nut thread	Performance level	Mod.	Dat.	Name

	Dat.	Name
Detail.	13/dec/00	ALSPACE
Insp.		
Stand.		



D-Sub, male, standard angle,
25 poles, with solder pin,
nut and hole

Maßstab/
Scale

1.5:1

HARTING EURL
F-95972 Paris



TB 0965322x80x

Blatt/ Page

2

Sub.

5


4

3

2


1

Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802




No.1 contact


screw lock thread



cavity



Printed board layout
component side




D

C

B

A

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, standard angle, 25 poles, with solder pin, screw lock and hole	Maßstab/ Scale 1.5:1
							Detail.	12/dec/00	ALSPACE		
							Insp.				
09 65 322 6803	4-40 UNC	2	29773	18-APR-02	CV		Stand.				
09 65 322 7803	4-40 UNC	3	29689	03/07/01	AA						
09 65 322 5803	4-40 UNC	0.76 µm Au	27960	12/dec/00	ALSPACE						
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name						
HARTING EURL F-95972 Paris										TB 0965322x80x Sub.	Blatt/ Page 3

09 65 322 5801

Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 322 5800
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	hole 3.1 mm
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 322 5802
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 322 5803
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt