


# MALE PCB PINS

## SOLDER TERMINALS SLOTTED

### 2314

2314-X-01-XX-00-00-07-0

Swage mount in 1,93 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2314-1            | 0,79            | 1,14     |
| 2314-2            | 1,57            | 2,39     |
| 2314-3            | 2,39            | 3,18     |
| 2314-4            | 3,18            | 3,96     |

### 2511

2511-X-01-XX-00-00-07-0

Swage mount in 1,93 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2511-1            | 0,79            | 1,60     |
| 2511-2            | 1,57            | 2,39     |
| 2511-3            | 2,39            | 3,18     |
| 2511-4            | 3,18            | 3,96     |

### 2515

2515-X-01-XX-00-00-07-0


Swage mount in 2,39 hole



### 2516

2516-X-01-XX-00-00-07-0

Swage mount in 2,39 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 251X-1            | 0,79            | 1,91     |
| 251X-2            | 1,57            | 2,67     |
| 251X-3            | 2,39            | 3,43     |
| 251X-4            | 3,18            | 3,73     |

### 2502

2502-X-01-XX-00-00-07-0

Swage mount in 2,39 hole



| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 2502-1            | 0,79            | 2,03     |
| 2502-2            | 1,57            | 2,82     |
| 2502-3            | 2,39            | 3,63     |
| 2502-4            | 3,18            | 4,42     |

#### SPECIFICATIONS:

**Pin Material:** Brass Alloy 360, 1/2 Hard  
( Swage pins are annealed )

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$   
Diameters:  $\pm 0,051$   
Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - 01 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER  
(60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com