

630-006

EMI/RFI Environmental Bulkhead Feed-Through with Strain Relief Front and Rear Panel Mount - Straight

Single Overall EMI/RFI Shield Termination

630 A 006 NF 16 2 A

Product Series ———

Fitting Type ———
A = Rear Mount
B = Front Mount






Basic Part No. ———

Finish (Table II) ———

Strain Relief Style (H, A, M, D)


Fitting Style
1 = RFI/EMI Only
2 = Environmental Only
3 = RFI/EMI Environmental
4 = Non-RFI/EMI Non-environmental

Cable Entry (Table III)




1. Metric dimensions (mm) are indicated in parentheses.
2. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.


STYLE H
Heavy Duty




STYLE A
Medium Duty



STYLE M
Medium Duty



STYLE D
Medium Duty



630-006
EMI/RFI Environmental Bulkhead Feed-Through
 with Strain Relief
 Front and Rear Panel Mount - Straight



63

See inside back cover fold-out or page 14 for Table II.

TABLE III: CABLE ENTRY																
Dash	Clamp		Cable Range				A Thread		B		C Sq.		D Dia -.000		E Dia -.000	
No.	Style	Size	Min		Max		Unified		Dim		± .010 (± .3)		+ .015 (+ .4)		+ .030 (+.8)	
01	1, 2	03	.157	(4.0)	.250	(6.4)	1/2 -28	.885	(22.5)	.593	(15.1)	.120	(3.0)	.250	(6.4)	
02	3	03	.157	(4.0)	.250	(6.4)	1/2 -28	.885	(22.5)	.593	(15.1)	.120	(3.0)	.250	(6.4)	
03	1,2	04	.187	(4.7)	.312	(7.9)	5/8 -24	1.104	(28.0)	.812	(20.6)	.120	(3.0)	.312	(7.9)	
04	3	04	.187	(4.7)	.312	(7.9)	5/8 -24	1.104	(28.0)	.812	(20.6)	.120	(3.0)	.312	(7.9)	
05	1, 2	06	.281	(7.1)	.437	(11.1)	3/4 -20	1.197	(30.4)	.906	(23.0)	.120	(3.0)	.437	(11.1)	
06	3	06	.281	(7.1)	.437	(11.1)	3/4 -20	1.197	(30.4)	.906	(23.0)	.120	(3.0)	.437	(11.1)	
07	1,2	08	.344	(8.7)	.562	(14.3)	7/8 -20	1.291	(32.8)	.968	(24.6)	.120	(3.0)	.562	(14.3)	
08	3	08	.344	(8.7)	.562	(14.3)	7/8 -20	1.291	(32.8)	.968	(24.6)	.120	(3.0)	.562	(14.3)	
09	1, 2	10	.375	(9.5)	.625	(15.9)	1 -20	1.385	(35.2)	1.062	(27.0)	.120	(3.0)	.625	(15.9)	
10	3	10	.375	(9.5)	.625	(15.9)	1 -20	1.385	(35.2)	1.062	(27.0)	.120	(3.0)	.625	(15.9)	
11	1,2	12	.438	(11.1)	.750	(19.1)	1 3/16 -18	1.635	(41.5)	1.250	(31.8)	.120	(3.0)	.750	(19.1)	
12	3	12	.438	(11.1)	.750	(19.1)	1 3/16 -18	1.635	(41.5)	1.250	(31.8)	.120	(3.0)	.750	(19.1)	
13	1, 2	16	.625	(15.9)	.937	(23.8)	1 7/16 -18	1.760	(44.7)	1.375	(34.9)	.147	(3.7)	.937	(23.8)	
14	3	16	.625	(15.9)	.937	(23.8)	1 7/16 -18	1.760	(44.7)	1.375	(34.9)	.147	(3.7)	.937	(23.8)	
15	1,2	20	.875	(22.2)	1.250	(31.8)	1 3/4 -18	2.010	(51.1)	1.562	(39.7)	.147	(3.7)	1.250	(31.8)	
16	3	20	.875	(22.2)	1.250	(31.8)	1 3/4 -18	2.010	(51.1)	1.562	(39.7)	.147	(3.7)	1.250	(31.8)	
17	1, 2	24	1.000	(25.4)	1.375	(34.9)	2 -18	2.260	(57.4)	1.750	(44.5)	.173	(4.4)	1.375	(34.9)	
18	3	24	1.000	(25.4)	1.375	(34.9)	2 -18	2.260	(57.4)	1.750	(44.5)	.173	(4.4)	1.375	(34.9)	
19	1,2	28	1.250	(31.8)	1.625	(41.3)	2 1/4 -16	2.510	(63.8)	1.938	(49.2)	.173	(4.4)	1.625	(41.3)	
20	3	28	1.250	(31.8)	1.625	(41.3)	2 1/4 -16	2.510	(63.8)	1.938	(49.2)	.173	(4.4)	1.625	(41.3)	
21	1, 2	32	1.437	(36.5)	1.875	(47.6)	2 1/2 -16	2.781	(70.6)	2.188	(55.6)	.173	(4.4)	1.875	(47.6)	
22	3	32	1.437	(36.5)	1.875	(47.6)	2 1/2 -16	2.781	(70.6)	2.188	(55.6)	.173	(4.4)	1.875	(47.6)	
23	1,2	40	1.875	(47.6)	2.375	(60.3)	3 -16	3.281	(83.3)	2.625	(66.7)	.173	(4.4)	2.375	(60.3)	
24	3	40	1.875	(47.6)	2.375	(60.3)	3 -16	3.281	(83.3)	2.625	(66.7)	.173	(4.4)	2.375	(60.3)	

TABLE III (Continued)													
Dash No.	Style	F Max		G Max		H Max		J Max		K Max		Length Max	
01	1, 2	---	---	---	---	.760	(19.3)	.843	(21.4)	.630	(16.0)	.971	(24.7)
02	3	---	---	---	---	.760	(19.3)	.843	(21.4)	.630	(16.0)	1.820	(46.2)
03	1,2	.780	(19.8)	.957	(24.3)	.760	(19.3)	.906	(23.0)	.755	(19.2)	.971	(24.7)
04	3	.780	(19.8)	.957	(24.3)	.760	(19.3)	.906	(23.0)	.755	(19.2)	1.820	(46.2)
05	1, 2	.780	(19.8)	1.145	(29.1)	.760	(19.3)	1.093	(27.8)	.942	(23.9)	.971	(24.7)
06	3	.780	(19.8)	1.145	(29.1)	.760	(19.3)	1.093	(27.8)	.942	(23.9)	1.820	(46.2)
07	1,2	.780	(19.8)	1.332	(33.8)	.760	(19.3)	1.187	(30.1)	1.067	(27.1)	.971	(24.7)
08	3	.780	(19.8)	1.332	(33.8)	.760	(19.3)	1.187	(30.1)	1.067	(27.1)	1.820	(46.2)
09	1, 2	.780	(19.8)	1.332	(33.8)	.760	(19.3)	1.281	(32.5)	1.192	(30.3)	.971	(24.7)
10	3	.780	(19.8)	1.332	(33.8)	.760	(19.3)	1.281	(32.5)	1.192	(30.3)	1.820	(46.2)
11	1,2	.811	(20.6)	1.551	(39.4)	.760	(19.3)	1.500	(38.1)	1.380	(35.1)	1.031	(26.2)
12	3	.811	(20.6)	1.551	(39.4)	.760	(19.3)	1.500	(38.1)	1.380	(35.1)	1.820	(46.2)
13	1, 2	.905	(23.0)	1.770	(45.0)	1.073	(27.3)	1.719	(43.7)	1.535	(39.0)	1.031	(26.2)
14	3	.905	(23.0)	1.770	(45.0)	1.073	(27.3)	1.719	(43.7)	1.535	(39.0)	1.820	(46.2)
15	1,2	1.092	(27.7)	2.113	(53.7)	1.323	(33.6)	2.062	(52.4)	1.848	(46.9)	1.031	(26.2)
16	3	1.092	(27.7)	2.113	(53.7)	1.323	(33.6)	2.062	(52.4)	1.848	(46.9)	1.820	(46.2)
17	1, 2	1.124	(28.5)	2.363	(60.0)	1.323	(33.6)	2.312	(58.7)	2.255	(57.3)	1.095	(27.8)
18	3	1.124	(28.5)	2.363	(60.0)	1.323	(33.6)	2.312	(58.7)	2.255	(57.3)	1.820	(46.2)
19	1,2	1.399	(35.5)	2.770	(70.4)	1.572	(39.9)	2.719	(69.1)	2.505	(63.6)	1.095	(27.8)
20	3	1.399	(35.5)	2.770	(70.4)	1.572	(39.9)	2.719	(69.1)	2.505	(63.6)	1.820	(46.2)
21	1, 2	1.399	(35.5)	3.020	(76.7)	1.572	(39.9)	2.969	(75.4)	2.755	(70.0)	1.095	(27.8)
22	3	1.399	(35.5)	3.020	(76.7)	1.572	(39.9)	2.969	(75.4)	2.755	(70.0)	1.940	(49.3)
23	1,2	---	---	---	---	1.572	(39.9)	3.531	(89.7)	3.255	(82.7)	1.220	(31.0)
24	3	---	---	---	---	1.572	(39.9)	3.531	(89.7)	3.255	(82.7)	2.060	(52.3)