






RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



SECTION A-A
SCALE:1:1

SPECIFICATIONS

1. Current rating: 1A AC, DC
2. Voltage rating: 50V AC, DC
3. Temperature range: -40°C ~ +105°C
4. Insulation resistance: 100MΩ Min.
5. Withstanding voltage: 500V AC/ minute.
6. Contact resistance: 20mΩ Max.

Material:

Insulator: PA9T UL 94V-0

Contact: Phosphor Bronze or Brass

Solder Tab: Brass

Plating: Matte Tin or gold plated over Nickel

Circuits: 02~12P

Mate with:XFCN P1010 series Housing


Ordering Code:

M1010VSF-XX
1 2

1.序列号

2. Pin位数 02-12P


No.of PIN/ROW	Dimension	
	A	B
02	4.00	1.00
03	5.00	2.00
04	6.00	3.00
05	7.00	4.00
06	8.00	5.00
07	9.00	6.00
08	10.00	7.00
09	11.00	8.00
10	12.00	9.00
11	13.00	10.00
12	14.00	11.00



PCB Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF XFCN AND SHALL
NOT BE REPRODUCED, COPIED OR CUED IN
ANY MANNER WITHOUT THE PRIOR
WRITTEN CONSENT OF XFCN

PART NO: M1010VSF-XX		XFCN兴飞连接器		
TITLE: 1.00mm Crimp Style Connectors		0769-82001899		
		www.xfconn.com		
		DWG NO: /		
APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.07.24	NONE	1/1	A1