





MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FED. MFR. CODE 91929SWITCH - TOGGLE
(MAGNETIC HOLD-IN)CATALOG LISTING
26ET55-2

NOTES

- 1 - EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIAL OR ARE SUITABLY PROTECTED TO PREVENT CORROSION. ENCLOSURE FINISHED WITH BLUE EPOXY BASED ENAMEL COLOR NO. 25184 PER FEDERAL STANDARD 595
- 2 - SWITCH SEALED PER MIL-S-5594
- 3 - HOLD IN VOLTAGE: THE MINIMUM SPECIFIED VOLTAGE AT WHICH THE LEVER WILL REMAIN ACTUATED. HOLD IN MAY OCCUR AT A LOWER VALUE.
DROP OUT VOLTAGE: THE VOLTAGE RANGE IN WHICH THE LEVER WILL BE RELEASED
- 4 - CIRCUITS CAN BE TRANSFERRED MANUALLY. ENERGIZING THE COIL WILL NOT CAUSE TRANSFER OF CIRCUITS
- 5 - CIRCUIT IDENTIFICATION IS SHOWN ON SWITCH
- 6 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 7 - HARDWARE MAYBE FURNISHED UNASSEMBLED PER MIL-S-5594

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
SOLENOID RATING AT 20° C		CONTACT ARRANGEMENT S P D T (2)		DO NOT SCALE PRINT	
STEADY STATE LIMITS-----	20-29 VDC	RATING IN AMPERES		UNLESS OTHERWISE SPECIFIED	
HOLD IN	15 VDC	SEA LEVEL		DIMENSIONS ARE IN INCHES	
DROP OUT	0-15 VDC	65,000 FT		TOLERANCES ARE:	
OVERRIDE FORCE AT 29 VDC----	10 LB MAX	RES IND MOTOR		ONE PLACE (.0) ±.030	
OPERATING FORCE-----	7 LB MAX	28 VOLTS DC		TWO PLACE (.00) ±.015	
COIL RESISTANCE-----	220 OHM MIN	RES IND MOTOR		THREE PLACE (.000) ±.005	
				ANGLES ±	
				WEIGHT 7.5 OZ MAX	