

PIN RECEPTACLES

PIN RECEPTACLES WITH ORGANIC FIBRE PLUG® SOLDER BARRIER (SEE SPECIFIC CONTACT RANGE ON PAGES 250, 251 & 253)

- These through-hole (tubular) receptacles are designed for hand, wave or reflow* soldering. The **ORGANIC FIBRE PLUG®** barrier prevents solder paste or flux from contaminating the spring contact.
- After soldering, the **OFP®** barrier is pushed out of the receptacle when the device is plugged in.
- All parts are available as discrete receptacles or supplied on carrier tape per EIA-481 to feed industry standard pick and place machines.


*Intrusive reflow (also called "pin-in-paste") is a technique of using conventional through-hole components in a reflow soldering process. The receptacles are placed into plated through-holes in the circuit board (solder paste has previously been screen printed on pads adjacent to the holes) and the board is reflowed in the same pass as other SMT components. Solder will fill the plated through-holes and achieve solder joints as reliable as wave soldering. The **OFP®** barrier prevents solder paste from being picked-up inside the contact during pick 'n place assembly. "Overprinting" paste on the solder mask can be used to adjust the volume of paste required to fill each hole.



4428

4428-0-XX-XX-04-XX-10-0


Solder mount in $\varnothing .032"$ max. PTH
#04 Contact for $\varnothing .008"$ - $.013"$ pins
 Also available on 16mm wide carrier tape:
 See page 194.15 for Tape & Reel details



5359

5359-0-XX-XX-10-XX-10-0


Solder mount in $\varnothing .043" \pm .003"$ PTH
#10 Contact for $\varnothing .012"$ - $.017"$ pins
 Also available on 16mm wide carrier tape:
 See page 194.15 for Tape & Reel details



0577

0577-0-XX-XX-21-XX-10-0


Solder mount in $\varnothing .045" \pm .003"$ PTH
#21 Contact for $\varnothing .015"$ - $.022"$ pins
 Also available on 12mm wide carrier tape:
 See page 194.15 for Tape & Reel details



4015

4015-0-XX-XX-30-XX-10-0

Solder mount in $\varnothing .057" \pm .003"$ PTH
#30 Contact for $\varnothing .015"$ - $.025"$ pins
 Also available on 8mm wide carrier tape:
 See page 194.15 for Tape & Reel details



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Solder Barrier: Organic Fibre Plug®

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
 Diameters: $\pm .002$
 Angles: $\pm 2^\circ$



ORDER CODE: XXXX - 0 - XX - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY PACKAGING:

43 Discrete Receptacles

67 Supplied on 13" Reels

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

◆ **27** 30 μ " GOLD OVER NICKEL (RoHS)

02 100 μ " TIN/LEAD OVER NICKEL

◆ **84** 100 μ " TIN OVER NICKEL (RoHS)

CONTACT:

#04, #10, #21 or #30 CONTACT (DATA ON PAGES 250, 251 & 253)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com