


# SERIES 621/622: D-SUB CONNECTOR

Plug and Receptacle, Right Angle, .318"(8.08mm) Footprint




- Two Contact Rows with .318"(8.08mm) Footprint Right Angle Bend
- .109"(2.77mm) Contact Spacing X .112"(2.84mm) Row Spacing
- Plug and Receptacle in 9, 15, 25, or 37 Contact Sizes
- Pin and Socket Contact Mating Design with P.C. Tail Termination
- Metal Shell Provides EMI/RFI Shielding, Plug Shell Indents provide Grounding and Additional Mating Retention
- Board Mounting Features include Threaded Hole, Two and Four Prong Boardlock for Superior Retention to P.C. Board
- Flange Mounting Options for Panel Mount or Connector Mating include Through Hole, Threaded Hole and Threaded Standoffs
- D-Shaped Connector Mating Outline provides Polarization
- Design based on Requirements of MIL-C-24038, EIA RS-232 and RS-449

## Specifications:

Insulator Material	Thermoplastic Polyester, UL 94V-0, Chemical Resistant, Color: Black
Contact Material	Plug (Pins): Copper Alloy Receptacle (Socket): Copper Alloy
Contact Plating	Selective Gold (See Ordering Code) over Nickel for the Mating Area, Tin Plating for Tail Area
Ferrite Specs:	20dB MIN @30 MHz, 30dB MIN @50 MHz, and 50dB MIN @100 MHz
Shell Material	Nickel Plated Steel
Current Rating	3A Per Contact
Contact Resistance	25 Milliohms MAX
Insulation Resistance	5000 Megaohms MIN
Dielectric Voltage	1000V AC rms at Sea Level
Operating Temp.	-55°C To +85°C
Mating Force	16 oz (4.45N) Maximum Per Contact Position
Unmating Force	1 oz (0.28N) Minimum Per Contact Position

## FLANGE MOUNTING OPTIONS



## Ordering Code:

621-025-260-013

SERIES: _____	621: PLUG (PIN)
622: RECEPTACLE (SOCKET)	_____
NO. OF CONTACTS: _____	009 - 9 CONTACTS      025 - 25 CONTACTS
015 - 15 CONTACTS	037 - 37 CONTACTS
CONTACT FINISH CODE: _____	2 - GOLD FLASH PLATING
3 - 15 MICROINCHES OF GOLD PLATING	6 - 30 MICROINCHES OF GOLD PLATING
CONTACT CODE: _____	60 - .318" FOOTPRINT CONTACT
68 - .318" FOOTPRINT WITH FERRITE FILTER	_____

### FLANGE MOUNTING OPTIONS:

- 0 - #4-40 THREADED FIXED STANDOFF
- 1 - Ø.120"(Ø3.05MM) THROUGH HOLE
- 2 - #4-40 THREADED HOLE
- 3 - #4-40 THREADED STANDOFF
- 5 - M3 THREADED HOLE
- 6 - M3 THREADED STANDOFF

### BOARD MOUNTING FEATURE:

- 1 - Ø.120"(Ø3.05MM) THROUGH HOLE
- 3 - TWO PRONG BOARDLOCKS
- 4 - FOUR PRONG BOARDLOCKS
- 5 - #4-40 THREADED HOLE



### INSULATOR MATERIAL CODE:

- 0 - STANDARD
- 5 - HIGH TEMP INSULATOR



# SERIES 621/622: D-SUB CONNECTOR

Plug and Receptacle, Right Angle, .318"(8.08mm) Footprint




## PLUG



RECOMMENDED P.C.B LAYOUT  
(FOR PLUG AND RECEPTACLE)



## RECEPTACLE



NUMBER OF CONTACTS	A±0.38mm Inch (mm)	B±0.25mm Inch (mm)	C±0.13mm PLUG Inch (mm)	C±0.13mm RECEPTACLE Inch (mm)
9	1.213 (30.81)	.984 (24.99)	.667 (16.92)	.643 (16.33)
15	1.543 (39.19)	1.312 (33.32)	.994 (25.25)	.971 (24.66)
25	2.088 (53.04)	1.852 (47.04)	1.534 (38.96)	1.511 (38.38)
37	2.729 (69.32)	2.500 (63.50)	2.182 (55.42)	2.159 (54.84)