

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	29JAN2016	JY	SH
	B	REVISED PER ECO-16-015248	24OCT2016	JY	SH
	C1	REVISED PER ECO-20-002129	14FEB2020	VM	SH
	D1	REVISED PER ECN-21-104118	17MAY2021	SH	SZ

1. MATERIAL:
CAGE MATERIAL : 0.25 THICK NICKEL SILVER.
SPRING MATERIAL: COPPER ALLOY
PURE COPPER FOIL: CONDUCTIVE, ADHESIVE

2. FINISH:
SPRING: NICKEL PLATING

3. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.

△4 REFERENCE APPLICATION SPEC 114-32023 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.

△5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.


6. MINIMUM PC BOARD THICKNESS: SINGLES SIDED: 1.57 MIN
DOUBLE SIDED: 2.20 MIN

△7 DATUM -A- IS TOP SURFACE OF THE HOST BOARD.



△8 DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN

△9 CUSTOMIZED SCHLEGEL GAP PAD.OP-8800.




△10 CUSTOMIZED PACKING TRAY.



SCALE 4:1



SCALE 4:1




△10	WITHOUT	WITHOUT	WITH	WITH	1	WITHOUT	6-2170703-4
	WITH	WITHOUT	WITH	WITHOUT	1	WITHOUT	1-2170703-4
△9	WITHOUT	WITH	WITH	WITHOUT	1	WITH LARGER	4-2170703-6
	WITHOUT	WITHOUT	WITH	WITH	0	WITH LARGER	2-2170703-9
	WITHOUT	WITHOUT	WITH	WITH	1	WITH LARGER	2-2170703-8
	WITHOUT	WITHOUT	WITH	WITHOUT	2	WITH LARGER	1-2170703-0
	WITHOUT	WITHOUT	WITH	WITH	1	WITHOUT	5-2170703-4
	WITHOUT	WITHOUT	WITH	WITH	2	WITH STANDARD	5-2170703-2
	WITHOUT	WITHOUT	WITHOUT	WITHOUT	0	WITH STANDARD	2-2170703-7
	WITHOUT	WITHOUT	WITH	WITHOUT	1	WITH LARGER	2-2170703-6
	WITHOUT	WITHOUT	WITH	WITHOUT	0	WITH STANDARD	2170703-7
	WITHOUT	WITHOUT	WITH	WITHOUT	1	WITH STANDARD	2170703-6
	WITHOUT	WITHOUT	WITH	WITHOUT	0	WITHOUT	2170703-5
	WITHOUT	WITHOUT	WITH	WITHOUT	1	WITHOUT	2170703-4
	WITHOUT	WITHOUT	WITH	WITHOUT	2	WITH STANDARD	2170703-2
	WITHOUT	WITHOUT	WITH	WITHOUT	2	WITHOUT	2170703-1
	COPPER FOIL	THERMAL PAD	SPRING FINGER	INSULATING TAPE OPTION	# REAR PINS	HEAT SINK OPEN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.25 3 PLC ± 0.20 4 PLC ± 0.100 ANGLES ± ° FINISH -		DWG. JASON YANG 23SEP2013 CHK. SEAN HAN 29JAN2016 APVD. -		NAME CAGE ASSEMBLY, QSFP28 1X1,THRU BEZEL WITH EMI SPRING FINGER	
MATERIAL -		WEIGHT -		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023		SIZE CAGE CODE DRAWING NO. A100779C= 2170703	
RESTRICTED CUSTOMER		SCALE 2:1		SHEET 1 OF 7		REV D1	


2170703-1 AS SHOWN

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-


HEAT SINK OPEN OPTIONS



WITHOUT HEAT SINK OPEN
SCALE 4:1




WITH STANDARD HEAT SINK OPEN (30.7X12.5)
SCALE 4:1




WITH LARGER HEAT SINK OPEN (35.5X15.25)
SCALE 4:1


OF REAR LEGS OPTIONS



2 REAR LEGS VERSION
SCALE 4:1




1 REAR LEG VERSION
SCALE 4:1




0 REAR LEG VERSION
SCALE 4:1

INSULATING TAPE OPTIONS



WITHOUT INSULATING TAPE
SCALE 3:1



INSULATING TAPE
(LXW = 33X18.55 REF)


5-2170703-2, 5-2170703-4, 2-2170703-8, 2-2170709-9
WITH INSULATING TAPE
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 23SEP2013	TE Connectivity	
		CHK: SEAN HAN 29JAN2016		
DIMENSIONS:		APVD: -	NAME	
mm			CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI SPRING FINGER	
		0 PLC ± 0.25	PRODUCT SPEC	
		1 PLC ± 0.25	108-19428	
		2 PLC ± 0.20	APPLICATION SPEC	
		3 PLC ± 0.100	114-32023	
MATERIAL		FINISH	WEIGHT	RESTRICTED TO
-		-	-	A 100779 C= 2170703
-		-	RESTRICTED CUSTOMER	SCALE 2:1 SHEET 2 OF 7 REV D1



REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-

SPRING FINGER OPTIONS


2-2170703-9



WITH EMI SPRING FINGER
SCALE 3:1






SCALE 3:1




SCALE 3:1

WITHOUT REAR EONS


2-2170703-8



SCALE 3:1



DETAIL A
SCALE 10:1




SEE DETAIL A

NOTE: 2-2170703-8 DIMENSIONS MARKED ARE FOR INSULATING TAPE


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. JASON YANG 23SEP2013	TE Connectivity
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK. SEAN HAN 29JAN2016	
DIMENSIONS:	mm	PRODUCT SPEC	NAME CAGE ASSEMBLY, OSFP28 1X1 THRU BEZEL WITH EMI SPRING FINGER
0 PLC	± 0.25	108-19428	
1 PLC	± 0.25	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO
2 PLC	± 0.20	114-32023	A100779C= 2170703
3 PLC	± 0.100	WEIGHT	RESTRICTED TO
4 PLC	± 0.100	RESTRICTED CUSTOMER	SCALE 2:1 SHEET 3 OF 7 REV D1
ANGLES	± 0.100		
FINISH	-		

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-




CUSTOMIZED THERMAL PAD
(LXWXH=32*13*0.5REF)
NOTES: PLS REMOVE THE
TRANSPARENT FILM BEFORE INSTALLATION

SCALE 3:1




4-2170703-6 AS SHOWN
SAME AS 2-2170703-6 EXCEPT WITH THERMAL PAD
SCALE 3:1

PURE COPPER FOIL OPTIONS







1-2170703-4
SCALE 3:1



SCALE 3:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. JASON YANG 23SEP2013	TE Connectivity	
		CHK. SEAN HAN 29JAN2016		
DIMENSIONS:		APVD. -	NAME	
mm		PRODUCT SPEC	CAGE ASSEMBLY, OSFP28 1X1, THRU	
		108-19428	BEZEL WITH EMI SPRING FINGER	
		APPLICATION SPEC	SIZE	
		114-32023	CAGE CODE	
		FINISH	DRAWING NO.	
MATERIAL		RESTRICTED CUSTOMER	A100779C= 2170703	
		SCALE 2:1	SHEET 4 OF 7	
		REV D1		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 23SEP2013		
		CHK: SEAN HAN 29JAN2016		
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI SPRING FINGER	
mm		PRODUCT SPEC: 108-19428	SIZE: CAGE CODE: DRAWING NO: 2170703	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC: 114-32023	RESTRICTED TO: 2170703	
0 PLC ± 0.25		WEIGHT: -	SCALE: 2:1	
1 PLC ± 0.25		RESTRICTED CUSTOMER	SHEET 5 OF 7	
2 PLC ± 0.20			REV: D1	
3 PLC ± 0.100				
4 PLC ± -				
ANGLES ± -				
FINISH ± -				


REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN APVD
-	-	SEE SHEET 1	-	-




RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 2 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1



RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1




RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1




DETAIL B
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN JASON YANG 23SEP2013	NAME	CAGE ASSEMBLY, OSFP28 1X1 THRU BEZEL WITH EMI SPRING FINGER
DIMENSIONS:		CHK SEAN HAN 29JAN2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO
	0 PLC ± 0.25		108-19428	RESTRICTED TO
	1 PLC ± 0.25		APPLICATION SPEC	A 100779 C= 2170703
	2 PLC ± 0.20		114-32023	SCALE 2:1 SHEET 6 OF 7 REV D1
	3 PLC ± 0.100		WEIGHT	
	4 PLC $\pm$		RESTRICTED CUSTOMER	
	ANGLES FINISH			

REVISIONS				
P.	LTR.	DESCRIPTION	DATE	OWN
-	-	SEE SHEET 1	-	-




RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 2 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1

RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



DETAIL C
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JASON YANG 23SEP2013	NAME: CAGE ASSEMBLY, QSFP28 1X1 THRU BEZEL WITH EMI SPRING FINGER	
DIMENSIONS:		CHK: SEAN HAN 29JAN2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE: CAGE CODE DRAWING NO	
Ø	0 PLC ± 0.25	108-19428	A 00779 2170703	
PLC	1 PLC ± 0.25	APPLICATION SPEC	RESTRICTED TO	
PLC	2 PLC ± 0.20	114-32023	SCALE 2:1 SHEET 7 OF 7 REV D1	
PLC	3 PLC ± 0.100	WEIGHT		
PLC	4 PLC ± -	RESTRICTED CUSTOMER		
ANGLES	FINISH			