

Actuator

704.411.01



<https://eao.com/p/704.411.01>

Your product:



704.411.01 Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 29 mm
Front bezel colour:	Nature

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lever shape:	short
Lever colour:	Black
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching angle:	90° right
Switching action:	Rest - Maintained
Mechanical lifetime:	≤2.5 Mio. cycles of operation
Weight:	0.034 kg
Switching positions:	2 positions

AMBIENT CONDITION

IP Protection: IP65 front side

Storage temperature: - 40 °C ... + 85 °C


OTHER

Short Description: Actuator, Ø 29 mm, optional illuminative, Black, short, Nature, Aluminium, anodised, Rest - Maintained


max. number of switching elements: 3

Hints: Max. 3 switching elements can be clipped on

Wiring diagrams:




Dimension drawings:



A = Screw terminal

Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Switching positions:

