







| DIMENSION |            |
|-----------|------------|
| Dim A     | NX5.08     |
| Dim B     | (N-1)X5.08 |

| Poles   | Tolerance |
|---------|-----------|
| 2p-6p   | ±0.15     |
| 7p-12p  | ±0.25     |
| 13p-18p | ±0.35     |
| 19p-24p | ±0.40     |



| SIGN                                           | DATE     | DESCRIPTION                                     | APPROVER |
|------------------------------------------------|----------|-------------------------------------------------|----------|
| △                                              | 3/22'06  | Hole size changed from 0.5mm to 1.3mm           | Tony     |
| △                                              | 01/12 07 | Soldering temperature changed from 245° to 250° | Tason    |
| △                                              | 01/12 07 | Part NO is Changed                              | Tason    |
| △                                              | 6/04'08  | Operating temperature is Changed                | Marvin   |
| △                                              | 6/04'08  | Body type is Changed                            | Marvin   |
| △                                              | 11/09'10 | Add is " VDE "                                  | Aaron    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                                                 |          |

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- Item 3 Wire guard solder pin: Copper, Tin plated
- Item 4 Terminal screw: Steel Zinc plating"- "slot type

- △ Electrical cULus / VDE
- Voltage rating : 300VAC / 450V
  - Current rating : 20A / 24A
  - Wire range : 0.2-2.5mm<sup>2</sup>
  - Solid wire(AWG) : 12-30
  - Stranded wire(AWG) : 12-30
  - Torque : 3.5 Lb-In / 0.5 N.m
  - Screw: M3
  - Wire strip length: 6-7mm
  - Withstanding Voltage: 1.6KV / 2.5KV
  - △ ● Operating temperature: -40°C to +115°C
  - △ ● Soldering temperature: 250°C±10°C/5 Sec
  - Safety Approval: cULus VDE

VJ xx 21 x 0 xxxx G

|                                   |                     |                                                                        |
|-----------------------------------|---------------------|------------------------------------------------------------------------|
|                                   |                     | RoHS                                                                   |
|                                   |                     | Pb<40,000ppm                                                           |
| No. of poles end stackable design | 0 Black (RAL9005)   | 0000:"@ "Logo (Standard )                                              |
|                                   | 2 Red (RAL3001/D)   | 000A:"ANYTEK"Logo                                                      |
| 02 2 CONTACTS                     | 3 Orange(RAL2011/P) | Any special item by customer request, please contact sales department. |
| 03 3 CONTACTS                     | 4 Yellow(RAL1018/A) |                                                                        |
| ... ..                            | 5 Green(RAL6018/T)  |                                                                        |
| 24 24 CONTACTS                    | 6 Blue (RAL5015/A)  |                                                                        |
|                                   | 8 Grey(RAL7035/D)   |                                                                        |

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |         |                                                   |                      |                                                                                       |              |            |
|----------|---------|---------------------------------------------------|----------------------|---------------------------------------------------------------------------------------|--------------|------------|
| TITLE    |         | VJ-5.08 Series 2P-24P Vertical ( 90D wire inlet ) |                      |                                                                                       |              |            |
| PART NO. |         | VJxx21x0xxxxG                                     |                      | DWG NO.                                                                               | 8VJ0102      |            |
| APPROVED | CHECKED | DESIGNED                                          | DRAWN                | CUST NO.                                                                              | Tolerance    |            |
|          |         | Aaron<br>2010.11.09                               | Marvin<br>2008.06.04 |  | UNIT: mm     | X. ±0.50   |
|          |         |                                                   |                      |                                                                                       | SCALE: NONE  | X.X ±0.30  |
|          |         |                                                   |                      |                                                                                       | SHEET: 01/01 | X.XX ±0.10 |
|          |         |                                                   |                      |                                                                                       | REV.: G      | X° ±1°     |