

Actuator

704.093.0



<https://eao.com/p/704.093.0>

Your product:



704.093.0
Actuator

FRONT

Front bezel material:	Aluminium
Front dimension:	Ø 29 mm
Front bezel colour:	Nature

MOUNTING

Design:	raised
----------------	--------

OPERATING-/INDICATION PART

Lever shape:	long
Lever colour:	Black
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

MECHANICAL CHARACTERISTIC

Switching action:	Maintained - Rest - Maintained
Mechanical lifetime:	≤2.5 Mio. cycles of operation
Switching positions:	3 positions
Weight:	0.034 kg
Switching angle:	42° left / 42° right


AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

OTHER

Hints:	Max. 3 switching elements can be clipped on
max. number of switching elements:	3
Short Description:	Actuator, Ø 29 mm, non illuminative, Black, long, Nature, Aluminium, anodised, Maintained - Rest - Maintained


Switching positions:



Wiring diagrams:




Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:



A = Screw terminal