


Relays, Contactors & Switches > Relays > Mil-Aero Relays > 1/5-Size Relays



Contact Arrangement: **2 Form C, DPDT, 2 C/O**

Input Voltage: **26.5 VDC**

Coil Suppression Diode: **Without**

Contact Current Rating: **2 A**

Coil Voltage Rating: **26.5 VDC**

## Features

### Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

### Configuration Features

Transistor Driver	Without
-------------------	---------

### Electrical Characteristics

Actuating System	DC
Vibration	30G's, 10 – 3000Hz
Coil Magnetic System	Non-Polarized, Monostable
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
Coil Polarity Protection Diode	Without
Input Voltage	26.5 VDC
Coil Suppression Diode	Without
Coil Voltage Rating	26.5 VDC
Coil Resistance	1350 Ω

Coil Power Rating (DC)	520 mW
------------------------	--------

#### Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Current Rating	2 A

#### Termination Features

Termination Type	PC Pins
------------------	---------

#### Mechanical Attachment

Mounting Type	Chassis Mount
---------------	---------------

#### Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

#### Product Compliance


For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 2-1617076-6  
 3SBH1231A2 = M39016/53-012M

## Also in the Series | CII 3SBC Relay



1/5-Size Relays(45)

## Customers Also Bought



TE Part #YDTS26W19-35SNC001  
 PLUG ASSY



TE Part #2-1617033-5  
 HFW1230G01P = M39016/6-112P



TE Part #1617125-2  
 JMAW-12XM = M39016/9-016M



TE Part #1577629-1  
 TERMINAL RT PIDG PEEK STRATO 20 AWG



TE Part #5221629-2  
 TERMINATOR,BNC,75 OHM,1 WATT



TE Part #  
 YACT20JC04SNV00100  
 SQUARE FLANGE  
 RECEPTACLE



TE Part #1-1617795-0  
 FCA-150-BY4=Relay



TE Part #1617351-5  
 J1MAW-12XM=M39016/7-019M



## Documents

### Datasheets & Catalog Pages

[5-1773450-5\\_sec1\\_3SBC](#)

English