




1	2	3	4	5	6	7																																																
				<table><tr><td>SIGN</td><td>DATE</td><td>DESCRIPTION</td><td>APPROVER</td></tr><tr><td>△</td><td>2009.09.09</td><td>The part No is changed</td><td>Jacke</td></tr><tr><td>△</td><td>2011.02.25</td><td>The wire is changed from 14-30(AWG) to 14-28(AWG)</td><td>Aaron</td></tr><tr><td>△</td><td>2011.02.25</td><td>Add is cULus</td><td>Aaron</td></tr><tr><td colspan="4">THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</td></tr></table>			SIGN	DATE	DESCRIPTION	APPROVER	△	2009.09.09	The part No is changed	Jacke	△	2011.02.25	The wire is changed from 14-30(AWG) to 14-28(AWG)	Aaron	△	2011.02.25	Add is cULus	Aaron	THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																															
SIGN	DATE	DESCRIPTION	APPROVER																																																			
△	2009.09.09	The part No is changed	Jacke																																																			
△	2011.02.25	The wire is changed from 14-30(AWG) to 14-28(AWG)	Aaron																																																			
△	2011.02.25	Add is cULus	Aaron																																																			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																						
				Material: ● Item a Clamp: Brass Ni plated ● Item b Male contact pin: Brass,Tin plated. ● Item c Terminal screw: Steel Zinc plating ● Item d Terminal housing: Thermoplastic (UL94V-0) ● Item e Terminal cover: Thermoplastic (UL94V-0) Electrical: cULus ● Voltage rating: 300V ● Current rating: 8A ● Wire range: △ ● Solid wire(AWG): 14-28 △ ● Stranded wire(AWG):14-28 ● Torque(Lb-In): 2.17 ● Screw:M2 ● Wire strip length:6 mm ● Withstanding Voltage:1.6KV ● Operating temperature: -40°C to +115°C △ ● Safety Approval:  V5 xx 31 x 0 xxxx G No. OF POLES 02 2 CONTACTS 03 3 CONTACTS 24 24 CONTACTS Color 0 Black (RAL9005) 2 Red (RAL3001/D) 3 Orange(RAL2011/P) 4 Yellow(RAL1018/A) 5 Green(RAL6018/T) 6 Blue (RAL5015/A) 8 Grey(RAL7035/D) G: Pb<40000ppm 0000: "@" Logo (Standard) 000A: "ANYTEK" Mark Any special item by customer request. please contact sales department.																																																		
																																																						
																																																						
																																																						
N = Number of poles Dim A=Nx3.81+1.39 Dim B=(N-1)x3.81 Dim C=Nx3.81+5.19 Dim D=Nx3.81+10.39 <table><tr><td></td><td>Dim A</td><td>Dim B</td><td>Dim C</td><td>Dim D</td></tr><tr><td>2-6p</td><td>±0.15</td><td>±0.15</td><td>±0.15</td><td>±0.15</td></tr><tr><td>7-12p</td><td>±0.20</td><td>±0.20</td><td>±0.20</td><td>±0.20</td></tr><tr><td>13-18p</td><td>±0.30</td><td>±0.30</td><td>±0.30</td><td>±0.30</td></tr><tr><td>19-24p</td><td>±0.35</td><td>±0.35</td><td>±0.35</td><td>±0.35</td></tr></table>					Dim A	Dim B	Dim C	Dim D	2-6p	±0.15	±0.15	±0.15	±0.15	7-12p	±0.20	±0.20	±0.20	±0.20	13-18p	±0.30	±0.30	±0.30	±0.30	19-24p	±0.35	±0.35	±0.35	±0.35																										
	Dim A	Dim B	Dim C	Dim D																																																		
2-6p	±0.15	±0.15	±0.15	±0.15																																																		
7-12p	±0.20	±0.20	±0.20	±0.20																																																		
13-18p	±0.30	±0.30	±0.30	±0.30																																																		
19-24p	±0.35	±0.35	±0.35	±0.35																																																		
				<table><tr><td colspan="2">TITLE</td><td colspan="4">V5 3.81 mm W/O Flange Bottom cover fixed type Series</td></tr><tr><td colspan="2">PART NO.</td><td colspan="2">V5xx31x0xxxxG △</td><td colspan="2">DWG NO.</td><td>8V50101</td></tr><tr><td>APPROVED</td><td>CHECKED</td><td>DESIGNED</td><td>DRAWN</td><td>CUST NO.</td><td colspan="2"></td></tr><tr><td></td><td></td><td>Aaron 2011.02.25</td><td>Jacke 2009.08.27</td><td></td><td>UNIT: mm</td><td>Tolerance</td></tr><tr><td colspan="4"></td><td>SCALE: NONE</td><td>X. ±0.50</td><td>X.X ±0.30</td></tr><tr><td colspan="4"></td><td>SHEET: 01/01</td><td>REV.: D</td><td>X.XX ±0.10</td></tr><tr><td colspan="4"></td><td></td><td></td><td>X° ±1°</td></tr></table>			TITLE		V5 3.81 mm W/O Flange Bottom cover fixed type Series				PART NO.		V5xx31x0xxxxG △		DWG NO.		8V50101	APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Aaron 2011.02.25	Jacke 2009.08.27		UNIT: mm	Tolerance					SCALE: NONE	X. ±0.50	X.X ±0.30					SHEET: 01/01	REV.: D	X.XX ±0.10							X° ±1°
TITLE		V5 3.81 mm W/O Flange Bottom cover fixed type Series																																																				
PART NO.		V5xx31x0xxxxG △		DWG NO.		8V50101																																																
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.																																																		
		Aaron 2011.02.25	Jacke 2009.08.27		UNIT: mm	Tolerance																																																
				SCALE: NONE	X. ±0.50	X.X ±0.30																																																
				SHEET: 01/01	REV.: D	X.XX ±0.10																																																
						X° ±1°																																																
1	2	3	4	5	6	7																																																