

8P1P YYY 2 1 0 YR BR 1

SERIES 14.00 [0.551]

OF POSITIONS (Ex. 002)
SEE CHART A

2 = FEMALE

BOARD MOUNT (PANEL MOUNT)

PLASTIC SHELL

1 = GOLD FLASH

RoHS COMPLIANT

NUT "B" COLOR
G = GREY
A = BLUE
J = YELLOW
N = BLACK
R = RED
V = GREEN

CHARACTERISTICS

MATERIALS





HOUSING : ABS+PC
HOUSING COLOR : GREY
NUT A : BRASS
NUT A PLATING : NICKEL
CONTACTS : COPPER ALLOY
CONTACT PLATING : 7μ" GOLD PLATED OVER 196μ" NICKEL MIN.
INSULATOR : PPS (HIGH TEMPERATURE)

MECHANICAL

DURABILITY: 2000 CYCLES
OPERATING TEMP. RANGE: -20° C ~ +120° C
PROCESS TEMPERATURE : 260° C FOR 5 SECONDS
MAX. TORQUE VALUE : 0.7 Nm [6.19 IN/lbs]

IP RATING: 50

****NOTE****
SEE PAGE 2 FOR BOARD LAYOUTS



CONTACT RESISTANCE = 10 mΩ
TEST VOLTAGE = 600V
WORKING VOLTAGE = 200V

PANEL CUTOUT

TOLERANCE = +0.10, -0.0
[+0.004, -0.00]

CHART A

● = KEY LOCATION


VIEW FROM TERMINATION END

2 POSITION 10 AMP MAX. PIN Ø = 1.30 [0.051]	3 POSITION 10 AMP MAX. PIN Ø = 1.30 [0.051]	4 POSITION 8 AMP MAX. PIN Ø = 0.90 [0.035]	5 POSITION 7 AMP MAX. PIN Ø = 0.90 [0.035]	6 POSITION 6 AMP MAX. PIN Ø = 0.70 [0.028]	7 POSITION 5 AMP MAX. PIN Ø = 0.70 [0.028]	8 POSITION 5 AMP MAX. PIN Ø = 0.70 [0.028]	9 POSITION 3 AMP MAX. PIN Ø = 0.50 [0.020]	10 POSITION 3 AMP MAX. PIN Ø = 0.50 [0.020]
CONTACT RESISTANCE = 5 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 5 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 1050V WORKING VOLTAGE = 350V	CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V	CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V

RoHS COMPLIANT











	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	NorComp	DRAWN: M. SIGMON	DATE: 10-11-16	SCALE: N.T.S.	SHEET 1	OF 2	REV: 2
						DWG NO. 8P1PYYY210YRBR1		

● = KEY LOCATION



HOLE DIAMETERS

2 POS : 0.90 [0.035]
 3-14 POS : 0.80 [0.031]

2 POS3 POS4 POS5 POS6 POS7 POS8 POS9 POS10 POS14 POS**RoHS COMPLIANT**

THESE DRAWINGS AND SPECIFICATIONS
 ARE THE PROPERTY OF NorComp AND
 SHALL NOT BE REPRODUCED, COPIED
 OR USED AS THE BASIS FOR THE
 MANUFACTURE OR SALE OF APPARATUS
 WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:
M. SIGMON

DATE:
10-11-16

SCALE:
N.T.S.

SHEET
2 OF 2

REV:
2

DWG NO.
8P1PYYY210YRBR1