



N= Number of poles Δ

DIM		TOL				
		2P-5P	6P-10P	11P-16P	17P-24P	25P-30P
Dim A	$(N+2) \times 7.62 + 1.5$	± 0.20	± 0.25	± 0.35	± 0.40	± 0.50
Dim B	$(N-1) \times 7.62$	± 0.20	± 0.25	± 0.35	± 0.40	± 0.50

SIGN	DATE	DESCRIPTION	APPROVER
Δ	11/21'12	Change the screw plating specification	Jacky
Δ	11/21'12	Change the dimensional tolerance	Jacky
Δ	11/21'12	Change the electrical specification	Jacky
Δ	11/21'12	Add the dimensional label	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:	250 V, 15 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 M Ω OR MORE AT DC 500 V
Δ OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	5.3 Lb-In.
WIRE RANGE:	22 - 16 AWG
1) MOLDED PARTS:	Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
Δ 3) TERMINAL SCREWS:	STEEL, M3

APPROVAL:

Critical dimension: ∇

YK 315 xx 3 x x 00 G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
:
30: 30 POLES

G: RoHS compliant (lead < 4%)
in copper alloy

MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
 Δ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
 Δ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-315 W/ Flange Series				
PART NO.	YK315xx3xx00G			DWG NO.	8YK0002-315
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacky 2012.11.21	Jacky 2012.11.21		Tolerance
					X. ± 0.50
					X.X ± 0.30
					X.XX ± 0.10
				SHEET: 01/01	REV.: C