





**CONNECTOR
DESIGNATORS**
A-F-H-L
**ROTATABLE
COUPLING**

Product Series	440	F	N	030	M	20	12-B	P	T	S	
Connector Designator											Slot Option (Omit if not required)
Angle and Profile											Shrink Boot (Table IV - Omit for none)
											Polysulfide (Omit for none)
											B = Band
											K = Precoiled Band (Omit for none)
Basic Part No.											Cable Entry (Table IV)
Finish (Table II)											Shell Size (Table I)

A Thread
Typ. (Table I)



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: ELBOW DIMENSIONS

Shell Size Conn. Desig. A-F-L H		E Max	F Max	G Max	H Max
08	09	.812 (20.6)	1.017 (25.8)	1.125 (28.6)	1.335 (33.9)
10	11	.875 (22.2)	1.071 (27.2)	1.250 (31.8)	1.460 (37.1)
12	13	.938 (23.8)	1.121 (28.5)	1.375 (34.9)	1.585 (40.3)
14	15	1.000 (25.4)	1.175 (29.8)	1.500 (38.1)	1.710 (43.4)
16	17	1.062 (27.0)	1.224 (31.1)	1.625 (41.3)	1.835 (46.6)
18	19	1.094 (27.8)	1.274 (32.4)	1.750 (44.5)	1.960 (49.8)
20	21	1.156 (29.4)	1.328 (33.7)	1.875 (47.6)	2.085 (53.0)
22	23	1.188 (30.2)	1.382 (35.1)	2.000 (50.8)	2.210 (56.1)
24	25	1.250 (31.8)	1.431 (36.3)	2.125 (54.0)	2.335 (59.3)

TABLE IV: CABLE ENTRY

Dash No.	K	L	M	Shrink Boot
01	.125 (3.2)	.250 (6.4)	.312 (7.9)	770-003S111
31	.188 (4.8)	.312 (7.9)	.374 (9.5)	770-003S111
02	.250 (6.4)	.375 (9.5)	.437 (11.1)	770-003S112
32	.312 (7.9)	.438 (11.1)	.500 (12.7)	770-003S112
03	.375 (9.5)	.500 (12.7)	.562 (14.3)	770-003S112
33	.438 (11.1)	.562 (14.3)	.624 (15.8)	770-001S104
04	.500 (12.7)	.625 (15.9)	.687 (17.4)	770-001S104
34	.562 (14.3)	.688 (17.5)	.750 (19.1)	770-001S104
05	.625 (15.9)	.750 (19.1)	.812 (20.6)	770-001S104
35	.688 (17.5)	.812 (20.6)	.874 (22.2)	770-001S104
06	.750 (19.1)	.875 (22.2)	.937 (23.8)	770-001S105
36	.812 (20.6)	.938 (23.8)	1.000 (25.4)	770-001S105
07	.875 (22.2)	1.000 (25.4)	1.062 (27.0)	770-001S105
37	.938 (23.8)	1.062 (27.0)	1.124 (28.5)	770-001S105
08	1.000 (25.4)	1.125 (28.6)	1.187 (30.1)	770-001S106
38	1.062 (27.0)	1.188 (30.2)	1.250 (31.8)	770-001S106
09	1.125 (28.6)	1.250 (31.8)	1.312 (33.3)	770-001S107
10	1.250 (31.8)	1.375 (34.9)	1.437 (36.5)	770-001S107
11	1.375 (34.9)	1.500 (38.1)	1.562 (39.7)	770-001S107
12	1.500 (38.1)	1.625 (41.3)	1.687 (42.8)	770-001S107
13	1.625 (41.3)	1.750 (44.5)	1.812 (46.0)	770-001S108
14	1.750 (44.5)	1.875 (47.6)	1.937 (49.2)	770-001S108
15	1.875 (47.6)	2.000 (50.8)	2.062 (52.4)	770-001S109
16	2.000 (50.8)	2.125 (54.0)	2.187 (55.5)	770-001S109

1. When maximum cable entry (page 21) is exceeded, Style 2 will be supplied. Dimensions E, F, G, and H will not apply. Please consult factory.
2. Metric dimensions (mm) are indicated in parentheses.
3. Interface O-Ring not supplied with Connector Designator A.
4. Consult factory for shorter lengths on straight backshells.
5. See page 40 for Shrink Boot Reference Information.
6. Backshells supplied with 600-052-* band, see Glenair Series 600 Tool Catalog for installation.