




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		E	REV PER ECO 12-009143	6-1-12	CT	DM

- 1 MATERIAL AND FINISH:\
- CONNECTOR SHELL: NICKEL PLATED ALUMINUM
- QUADRAX RETENTION CLIP: SILVER PLATED STAINLESS STEEL
- QUADRAX CONNECTOR: GOLD PLATED COPPER ALLOY AND BRASS, AND THERMOPLASTIC
- PERIPHERAL SEAL: FLUOROSILICONE RUBBER
2. OPERATING TEMPERATURE RANGE:
- 65°C TO +125°C (-85°F TO +257°F)
- 3 TE PART NUMBER, (00779), DATE CODE AND TE LOGO OR TE
- MARKED IN APPROXIMATE AREA SHOWN.




SECTION A-A



OLIVE DRAB	B	1954353-9
OLIVE DRAB	A	1954353-8
OLIVE DRAB	N	1954353-7
NICKEL	B	1954353-3
NICKEL	A	1954353-2
NICKEL	N	1954353-1
SHELL FINISH	M38999 KEY POLARIZATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG 24AUG2006	TE Connectivity			
DIMENSIONS: INCHES		CHK L OH 24AUG2006				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L OH 24AUG2006	NAME ASSY, RECEP, PCB, KIT, SIZE 21, 4Q4, M38999 STYLE, SERIES III			
0 PLC ±		PRODUCT SPEC	SIZE			
1 PLC ±		APPLICATION SPEC	CAGE CODE			
2 PLC ±.01		WEIGHT	DRAWING NO			
3 PLC ±.005		CUSTOMER DRAWING	RESTRICTED TO			
4 PLC ±.0020			SCALE			
ANGLES ±1°			SHEET			
FINISH			OF			
			REV			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



PIN NUMBER	SIGNAL ALLOCATION
1	Tx+
2	Rx+
3	Tx-
4	Rx-
PIN LOCATIONS GO CLOCKWISE FROM POSITION 1	

