






LOC	DIST	REVISIONS					
AF	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECR-15-014244	22SEP2015	NK	DC




- ① POLYAMIDE, UL94-V0, COLOR: NATURAL (WHITE)
- 2 GLOW WIRE FLAMMABILITY INDEX (GWFI) 850°C AT LEAST ACC. TO IEC 60335-1
- 3 GLOW WIRE IGNITION TEMPERATURE (GWIT) 775°C AT LEAST, ACC. TO IEC 60335-1
- 4 GLOW WIRE END PRODUCT TEMPERATURE (GWEPT) 750°C NO FLAME, ACC. TO IEC 60335-1



SCALE 3:1
FOR -2 PART ONLY

51.60	24	2-2296205-4
47.40	22	2-2296205-2
43.20	20	2-2296205-0
39.00	18	1-2296205-8
34.80	16	1-2296205-6
30.60	14	1-2296205-4
26.40	12	1-2296205-2
22.20	10	1-2296205-0
18.00	8	2296205-8
13.80	6	2296205-6
9.60	4	2296205-4
5.40	2	2296205-2
DIM L	NO. OF POS	PART NO.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K		22SEP2015		POS		REV	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK CHIARELLI, DAVIDE		22SEP2015		TE Connectivity	
		APVD CHIARELLI, DAVIDE		22SEP2015		NAME		RECEPTACLE HOUSING, VAL-U-LOK, GLOW WIRE AND VO	
		0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ±		PRODUCT SPEC		SIZE		CAGE CODE	
		ANGLES ± FINISH		APPLICATION SPEC		DRAWING NO		RESTRICTED TO	
MATERIAL		WEIGHT		114-13172		A200779		C-2296205	
		-		Customer Drawing		SCALE 3:1		SHEET 1 OF 1	
								REV A	