




DETAIL D
SCALE 20



KNOB
SIZE 22 ONLY
TYPE I

.015 ± .005 X 45° ± 5 CHAMFER
(OPTIONAL .020 R MAX.)



TYPE I

.005 MAX
BOTH ENDS

Ø A
SEE NOTE 2

.015 ± .005 X 45° ± 5°
2 PLACES

TYPE II



OPTIONAL DESIGN FOR 10-405996-03
(MS27488-0-3)

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

SIZE	FSCM NO.	DOCUMENT NO.	REV.
C	77820	10-405996	K
SCALE: 10.0		REF: 10-101033	SHEET 2 OF 2