

MAX solutions

New Mill-Max SMT Spring-Loaded Connector Products



Mill-Max is pleased to announce the development of several new SMT Spring-Loaded Connectors (SLCs). All are offered as discrete contacts and many are available in tape and reel packaging.

New Mill-Max part family 0910-0 and 0910-1 through -4 are discrete SLCs specifically designed for production tape and reel assembly.

Part 0967 is a horizontal mount SMT SLC designed for low-profile board to board interconnections.

New Mill-Max part family 0990-0 and 0990-1 through -4 and 0997-0 through -9 are discrete SLCs featuring a large base utilized for either increased PCB stability or assembly in non-PCB applications such as a face plate. These part families offer a range of application heights from .137" to .430" (3,48mm to 10,92mm.)

For further information visit: mill-max.com/PR603.

(12/09 -- 561, 603)

Mill-Max Mfg. Corp. • 190 Pine Hollow Road, Oyster Bay, NY 11771-0300
516-922-6000 • Fax: 516-922-9253 • www.mill-max.com






SPRING-LOADED CONNECTORS Discrete Spring-Loaded Contacts




0900-0



0900-0-00-00-00-00-11-0
Short Stroke, Surface mount
Lowest profile


0900-1⇒4



0900-X-00-00-00-00-11-0
Standard Stroke, Surface mount
Low profile


Basic Part Number	Length A
0900-1	.177
0900-2	.197
0900-3	.217
0900-4	.236

0934




0934-0-15-20-74-14-26-0
Standard Stroke
Surface mount

0936




0936-0-15-20-75-14-11-0
Standard Stroke
Surface mount

0928



0928-0-15-20-77-14-11-0
Long Stroke
Surface mount


0907-0⇒9



0907-X-15-20-75-14-11-0
Standard Stroke, Surface mount
High profile


Basic Part Number	Length A
0907-0	.255
0907-1	.275
0907-2	.295
0907-3	.315
0907-4	.335
0907-5	.350
0907-6	.370
0907-7	.390
0907-8	.410
0907-9	.430

0913




0913-0-15-20-77-14-11-0
Long Stroke
Surface mount

0925




0925-0-15-20-73-14-26-0
Standard Stroke
Surface mount

0927



0927-0-15-20-75-14-11-0
Standard Stroke
Surface mount

0905



0905-0-00-00-00-00-11-0
Standard Stroke, Surface mount
Highest Profile

ORDER CODE: 09XX - X - 15 - 20 - 7X - 14 - XX - 0

Spring Number

MATERIAL SPECIFICATIONS:

SLEEVE & PLUNGER MATERIAL: Copper Alloy
SPRING MATERIAL: Beryllium Copper
SLEEVE & PLUNGER FINISH: 20 μ " Gold over Nickel
SPRING FINISH: 10 μ " Gold over Nickel
DIMENSION IN INCHES:
TOLERANCES ON: LENGTHS: $\pm .006$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$



MECHANICAL & ELECTRICAL SPECIFICATIONS:

DURABILITY: 1,000,000 cycles

CURRENT RATING: 2A continuous, 3A peak

CONTACT RESISTANCE: 20 m Ω max.

SPRING NUMBER	Mid. STROKE	Max. STROKE	FORCE @ Mid. Stroke	Initial Force (Pre-load)
73	.0275	.055	60	25
74	.0275	.055	50	15
75	.0275	.055	60	25
77	.045	.090	60	25


73, 74, 75, 77 Springs are not Interchangeable



SPRING-LOADED CONNECTORS Discrete Spring-Loaded Contacts




0910-0



0910-0-57-20-76-14-11-0

Short Stroke, Surface mount
Packaged on 16mm wide carrier
tape: 1,500 parts per 13" reel.

0910-1⇒4



0910-X-57-20-75-14-11-0


Standard Stroke, Surface mount
Packaged on carrier tape.
See chart for tape width and qty. per reel



Basic Part Number	Length A
0910-1	.177
0910-2	.197
0910-3	.217
0910-4	.236


Basic Part Number	Tape Width	Quantity per Reel
0910-1	16mm	1,500
0910-2	24mm	1,100
0910-3	24mm	1,100
0910-4	24mm	1,100

0967




0967-0-15-20-75-14-11-0


Standard Stroke, Horizontal Surface mount
Also available on 16mm wide carrier
tape: 2,200 parts per 13" reel.
Order as: 0967-0-58-20-75-14-11-0



P.C.B. Layout




0990-0



0990-0-50-20-76-14-11-0

Short Stroke, Surface mount
Large Base

0990-1⇒4




0990-X-50-20-75-14-11-0

Standard Stroke, Surface mount
Large Base

Basic Part Number	Length A
0990-1	.177
0990-2	.197
0990-3	.217
0990-4	.236

0997-0⇒9



0997-X-50-20-75-14-11-0

Standard Stroke, Surface mount
Large Base

Basic Part Number	Length A
0997-0	.255
0997-1	.275
0997-2	.295
0997-3	.315
0997-4	.335
0997-5	.350
0997-6	.370
0997-7	.390
0997-8	.410
0997-9	.430

ORDER CODE: 09XX - X - XX - 20 - 7X - 14 - 11 - 0

Spring Number →

MATERIAL SPECIFICATIONS:

SLEEVE & PLUNGER MATERIAL: Copper Alloy
SPRING MATERIAL: Beryllium Copper
SLEEVE & PLUNGER FINISH: 20 μ" Gold over Nickel
SPRING FINISH: 10 μ" Gold over Nickel
DIMENSION IN INCHES:
TOLERANCES ON: LENGTHS: ±.006
DIAMETERS: ±.002
ANGLES: ± 2°



MECHANICAL & ELECTRICAL SPECIFICATIONS:

DURABILITY: 1,000,000 cycles
CURRENT RATING: 2A continuous, 3A peak
CONTACT RESISTANCE: 20 mΩ max.

SPRING NUMBER	Mid. STROKE	Max. STROKE	FORCE @ Mid. Stroke	Initial Force (Pre-load)
75	.0275	.055	60	25
76	.0195	.039	60	25

75 & 76 Springs are not interchangeable