

## SUMMARY

### # Wires

|             |   |
|-------------|---|
| Low voltage | 2 |
|-------------|---|



*Image is for illustrative purpose only*

|                  |                                |
|------------------|--------------------------------|
| Series           | 2K                             |
| Termination type | Male solder                    |
| IP rating        | 68                             |
| AWG wire size    | 22.00 - 14.00                  |
| Cable Ø          | 4.60 - 5.00 mm                 |
| Status           | active                         |
| Matching parts   | <a href="#">EGG.2K.302.CLL</a> |

### Download

[Request a quote](#)  
[Eplan](#)  
[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | FG*: Straight plug, cable collet                                                                                              |
| Keying            | 1 key (alpha=0, plug: male contacts, receptacle: female contacts)                                                             |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 41.16 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 2K.302 : 2 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 25 Amps                   |

### Specifications

Contact Type: Solder  
Contact Dia.: 2 mm (0.079in)  
Bucket Dia.: 1.8 mm (0.071in)  
Max. Solid Conductor: 1.5 mm<sup>2</sup> (AWG 14)  
Max. Stranded Conductor: 1.5 mm<sup>2</sup> (AWG 16)  
R (max): 3.3 mOhm  
Vtest (contact-shell): 1750 V (AC), 2500 V (DC)  
Vtest (contact-contact): 2100 V (AC), 2970 V (DC)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Others

Endurance (Shell): 5000 mating cycles  
Temp (min / max): -55°C / +200°C  
Humidity (max): <=95% [at 60 deg C /140 F]  
Vibration: 15 g [10 Hz - 2000 Hz]  
Shock Resistance: 100 g [ 6 ms]  
Climatical Category: 50/175/21  
Shielding (min): 95 dB (10 MHz)  
Shielding (min): 80 dB (1 GHz)  
Salt Spray Corrosion: >1000 hr

---

## DRAWINGS



## Dimensions

|     | A    | L    | M    | S2   |
|-----|------|------|------|------|
| mm. | 16   | 52   | 36   | 12   |
| in. | 0,63 | 2,05 | 1,42 | 0,47 |

---

## RECOMMENDED BY LEMO

### Tools

Spanner wrench: [DCD.2E.020.PA120](#)

Caps: [BFG.2K.100.NAS](#)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cables

|                    |               |       |                                                                                     |
|--------------------|---------------|-------|-------------------------------------------------------------------------------------|
| CMN.02.T20.047PGZE |               | Grey  |  |
| CMN.02.T20.047PNZE |               |       |  |
| CMN.02.T20.048QGZE | TPR (medical) | Grey  |  |
| 120240             | PVC           | Black |  |
| 120501             | PVC           | Grey  |  |
| 2221               | PVC           | Black |  |
| 4082               | PVC           | Grey  |                                                                                     |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.