












8		7		6		5		4		3		2		1									
CATALOG NO.		TERMINAL TYPE		IP20 FINGER SAFE C		NO. OF POLES																	
				W/O INDICATION												INDICATION							
HM25030-1SR		SCREW		CVR-RH-25030		CVRI-RH-25030										1							
HM25030-2SR		SCREW														2							
HM25030-3SR		SCREW														3							
HM25030-1PR		PRESSURE PLATE														1							
HM25030-2PR		PRESSURE PLATE														2							
HM25030-3PR		PRESSURE PLATE														3							
HM25030-1CR*		BOX LUG														1							
HM25030-2CR*		BOX LUG														2							
HM60030-3CR*		BOX LUG														3							
HM25030-1QR		SCREW AND .187 QUICK CONNECTS														1							
HM25030-2QR		SCREW AND .187 QUICK CONNECTS														2							
HM25030-3QR		SCREW AND .187 QUICK CONNECTS														3							
* -CHR ALSO AVAILABLE; SEE NOTE 10																							
																							
																							
HM25030-1SR		HM25030-1PR		HM25030-1QR																			




**CLOSING**  
PUSH STRAIGHT DOWN UNTIL SNAPS CLICK INTO PLACE





**OPENING**  
PULL STRAIGHT UP AT BOTH OUTSIDE HANDLES

CUT COVER TAB AT NOTCH FOR WIRES LARGER THAN 8 AWG




DETAIL A  
SCALE 4 : 3



1. HOOK DIN RAIL SNAPS ON ONE SIDE OF THE DIN RAIL

2. PUSH DOWN TO DEFLECT THE SNAPS



3. ROTATE UNTIL THE OPPOSITE SIDE SNAPS ONTO DIN RAIL

**INSTALLATION ON DIN RAIL**  
END STOPS MAY BE NECESSARY FOR SOME ASSEMBLY CONDITIONS - SEE NOTE 7

**EAT•N** BUSSMANN  
SERIES

TITLE  
**250V / 30AMP CLASS R & H FUSE BLOCK**

SIZE <b>A3</b>	DWG NO. <b>RM25030-HM25030-SERIES-CP</b>	REV <b>B</b>
-------------------	---	-----------------

SCALE: 2:3 SHEET 3 OF 3