






P	LTR	DESCRIPTION	DATE	DWN	APVD
A		FIRST RELEASE	7AUG20	C. X	D. Z

NOTES:


- 1 MATERIAL: CONTACT - BRASS
METAL PEG - BRASS
HOUSING - UL94V-0 RATED HIGH TEMP NYLON;
- 2 PLATING: CONTACT - 2.0um MINIMUM TIN OVER 1.27um MINIMUM NICKEL,
LEAD FREE PLATING;
METAL PEG - 2.0um MINIMUM TIN OVER 1.27um MINIMUM NICKEL,
LEAD FREE PLATING;
3. PRODUCT COMPLY WITH IEC60335-1 SECTION30(GWT)GLOW WIRE REQUIREMENTS.
4. PART NUMBER AND MATING PARTS ARE SHOWN IN TABLE OF SHEET 2;



SECTION A-A



RECOMMENDED PCB LAYOUT




10P	24.50
9P	22.50
8P	20.50
7P	18.50
6P	16.50
5P	14.50
4P	12.50
3P	10.50
2P	8.50
POSITION	DIM.A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. XU 9MAY2019	TE Connectivity		
DIMENSIONS: mm		CHK D. ZHANG 10MAY2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD D. ZHANG 10MAY2019	NAME HEADER ASSEMBLY, RIGHT ANGLE SGI2.0,SMT		
MATERIAL		PRODUCT SPEC 108-106266	SIZE A200779		
		APPLICATION SPEC 114-106266	CAGE CODE C-2336678		
		WEIGHT -	DRAWING NO -		
		RESTRICTED CUSTOMER	RESTRICTED TO		
		SCALE 4:1	SHEET 1 OF 3		
			REV A		

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD


2P/3P/4P/5P TAPE SHOWN


➡ USER DIRECTION OF UNREELING



6P/7P/8P/9P/10P TAPE SHOWN

➡ USER DIRECTION OF UNREELING



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. XU 9MAY2019	 TE Connectivity	
DIMENSIONS:		CHK D. ZHANG 10MAY2019		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. ZHANG 10MAY2019	NAME HEADER ASSEMBLY, RIGHT ANGLE SGI2.0,SMT	
	0 PLC ± 1 PLC ± 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-106266 APPLICATION SPEC 114-106266 WEIGHT -	SIZE A200779	CAGE CODE C-2336678-C
MATERIAL 		RESTRICTED CUSTOMER	SCALE 4:1	SHEET 3 OF 3
			REV A	