

FED MFG CODE 01020

CATALOG LISTING	
64AT300 SERIES	
CHART 2	

CATALOG LISTING 	KEYWAY POSITION		CENTER POSITION		OPPOSITE KEYWAY POSITION		RECOMMENDED LOCKING COMBINATIONS
	C-NC	C-NO	C-NO	C-NC	C-NC	C-NO	
64AT300-1	1, 2	3, 4	NONE	ALL	3, 4	1, 2	A,B,D,E,F,G,H,J,K,L,M,N,P
64AT300-3	1, 2	3, 4	NONE	NONE	3, 4	1, 2	D,F,G
64AT300-5	1, 2 *	3, 4 *	NONE	ALL	3, 4	1, 2	E,F,K,L,M,N
64AT300-7	1, 2 *	3, 4 *	NONE	ALL	3, 4 *	1, 2 *	E,L,N

* ASTERISK DENOTES MOMENTARY POSITION





Diagram illustrating the assembly of four switches (SWITCH NO. 1, SWITCH NO. 2, SWITCH NO. 3, SWITCH NO. 4) mounted on a common base. The switches are arranged in two rows of two. The maximum height of the assembly is indicated as .670 MAX.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



DO NOT SCALE PRINT

DO NOT SCALE PRINT

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNITS NOTED TO THE RIGHT ARE IN

REFERENCE UNLESS NOTED TOLERANCES ARE 1			
DIM		TOL.	

	DATE	TIME	IN	OUT
NO PLACES	X	1/04		
ONE PLACE	X X	0 4/ 018	X X	0 8/ 03
TWO PLACES	X XX	0 15/ 008	X XX	0 36/ 01
THREE PLACES			X XXX	0 13/ 08

[illegible]

DESIGN UNITS ☐ METRIC ☐ US CUSTOMARY ☒

DESIGN UNITS

WAS MATERIAL-COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE
 CUTTING OF STEEL

PROTECTIVE COATINGS ARE APPLIED

WEIGHT .09 LB EST

2.5

WEIGHT .09 LB EST